

规 格 书

SPECIFICATION

客户 CUSTOMER	立创商城
客户料号 CUSTOMER P/N	C7501332
规格描述 DESCRIPTION	250VAC/6UF/卧式/L15/黄色扁形/47*16.5*10/ZNRC
产品编码 PART NUMBER	HMP-605P250VAC
日期 DATE	2025-11-25

德尔创承认栏 APPROVED BY DERSONIC			客户承认栏 APPROVED BY CUSTOMER	
批 准 APPROVED BY	审 核 CHECK BY	制订 FORMULATE BY	批 准 APPROVED BY	审 核 CHECK BY
				

东莞市德尔创电子有限公司

DONGGUAN DERSONIC ELECTRONIC CO., LTD.




中国广东省东莞市寮步镇松湖智谷科技产业园2栋15楼
15/F, Building 2, Songhu Zhigu Science and Technology Industrial Park,
Liaobu Town, Dongguan City, Guangdong Province, China
TEL: +86-769-8533 5208 FAX: +86-769-8155 5989
Website: <http://www.dersonic.com>

D

C

B

A

876			54321					
TECHNICAL PARAMETERS			PRODUCT DIMENSIONS					CUSTOMER P/N
ELECTRICAL CHARACTERISTICS :			HMP-605P250VAC	Dimension(mm)				
				W (Max)	H (Max)	T (Max)	L (Min)	
1	Rated capacitance(C _R)	6.0μF		47.0	16.5	10.0	13.5	0.8
2	Capacitance tolerance	+10/-0%						
3	Rated voltage(VR)	250VAC						
4	Rated frequency	50/60Hz						
TEST PARAMETERS :								
5	Voltage test between terminals	VR*1.5 VDC/10s						
6	Tangent of the loss	0.002(1KHz20℃)						
7	Insulation Resistance	≥5,000 Mohm*μF (C>0.33μF) (100VDC 60S)						
WORK ENVIRONMENT :								
8	Operating Tempperature Range (case)	-40~90℃						
9	Accord with	ROHS						
10	Reference Standard	UL810						
CONSTRUCTION:								
11	Dielectric	Metallized Polypropylene Film						
12	Metal spray	Special Solder						
13	Filler	Epoxy resin (UL 94V-0)						
14	Outer envelope	Mylar Tape						
15	Lead wire	Lead wire Diameter 0.8mm						
Other								
876			54321					

D

C

B

A