


1. Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- Ideally suited for use in very high frequency switching power supplies, inverters and as a free wheeling diode
- Ultrafast recovery time for high efficiency
- Soft recovery characteristics
- Excellent high temperature switching
- Glass passivated junction
- High temperature soldering guaranteed: 250°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

2. Mechanical Data

- Case: JEDEC DO-214AC, molded plastic body over passivated chip
- Terminals: Axial leads, solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end
- Mounting Position: Any
- Weight: 0.012 ounce, 0.34 gram

3. Pinning information





4. Maximum Ratings And Electrical Characteristics

Parameter	Symbol	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Units					
Peak Repetitive Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V					
Working Peak Reverse Voltage	V_{RWM}	35	70	140	280	420	560	700						
DC Blocking Voltage	V_R	50	100	200	400	600	800	1000						
Average Rectified Output Current @ $T_J=75^\circ C$	I_o	1						A						
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave Superimposed on Rated Load (JEDEC Method)	I_{FSM}	30						A						
Forward Voltage Drop	V_{FM}	1		1.3		1.7		V						
Peak Reverse Current at Rated DC Blocking Voltage	I_{RM}	5						μA						
		100						μA						
Reverse Recovery Time (Note 2)	t_{rr}	50			75			ns						
Typical Junction Capacitance (Note 1)	C_J	20			10			pF						
Typical Thermal Resistance, Junction to Terminal	R_{eJT}	30						$^\circ C/W$						
Junction and Storage Temperature Range	T_J, T_{STG}	-65 to 150						$^\circ C$						


Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Notes:


1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
2. Measured with $I_F = 0.5A$, $I_R = 1.0A$, $I_{rr} = 0.25A$.



5.Typical characteristic



6.SMA Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	b	c	D	E	e1	L	K	θ
Min	1.95	0.77	0.97	1.10	4.95	2.00	2.09	1.38	1.95	4.25	2.60	0°
Max	2.05	0.83	1.03	1.30	5.15	2.20	2.19	1.42	2.05	4.35	2.65	5°

Notes: e-H<0.15mm



7 .Ordering information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW US1A	US1A	SMA	2000	Tape and reel
UMW US1B	US1B	SMA	2000	Tape and reel
UMW US1D	US1D	SMA	2000	Tape and reel
UMW US1G	US1G	SMA	2000	Tape and reel
UMW US1J	US1J	SMA	2000	Tape and reel
UMW US1K	US1K	SMA	2000	Tape and reel
UMW US1M	US1M	SMA	2000	Tape and reel



8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.