

规 格 书

SPECIFICATION



客户 CUSTOMER	立创商城
客户料号 CUSTOMER P/N	C7501331
规格描述 DESCRIPTION	250VAC/5UF/卧式/L15/黄色扁形/47*15.5*9/ZNRC
产品编码 PART NUMBER	HMP-505P250VAC
日期 DATE	2025-11-25

德尔创承认栏 APPROVED BY DERSONIC			客户承认栏 APPROVED BY CUSTOMER	
批 准 APPROVED BY	审 核 CHECK BY	制订 FORMULATE BY	批 准 APPROVED BY	审 核 CHECK BY
				

东莞市德尔创电子有限公司

DONGGUAN DERSONIC ELECTRONIC CO., LTD.

中国广东省东莞市寮步镇松湖智谷科技产业园2栋15楼
15/F, Building 2, Songhu Zhigu Science and Technology Industrial Park,
Liaobu Town, Dongguan City, Guangdong Province, China
TEL: +86-769-8533 5208 FAX: +86-769-8155 5989
Website: <http://www.dersonic.com>

8			7			6			5			4			3			2			1		
TECHNICAL PARAMETERS						PRODUCT DIMENSIONS									CUSTOMER P/N								
ELECTRICAL CHARACTERISTICS :						Dimension(mm)																	
						W (Max)	H (Max)	T (Max)	L (Min)	φd ±0.05													
1	Rated capacitance(C _R)	5.0μF	HMP-505P250VAC						47.0	15.5	9.0	13.5	0.8										
2	Capacitance tolerance	+10/-0%																					
3	Rated voltage(VR)	250VAC																					
4	Rated frequency	50/60Hz																					
TEST PARAMETERS :																							
5	Voltage test between terminals	VR*1.5 VDC/10s																					
6	Tangent of the loss	0.002(1KHz20℃)																					
7	Insulation Resistance	≥5,000 Mohm*μF (C>0.33μF) (100VDC 60S)																					
WORK ENVIRONMENT :																							
8	Operating Tempperature Range (case)	-40~90℃																					
9	Accord with	ROHS																					
10	Reference Standard	UL810																					
CONSTRUCTION :																							
11	Dielectric	Metallized Polypropylene Film																					
12	Metal spray	Special Solder																					
13	Filler	Epoxy resin (UL 94V-0)																					
14	Outer envelope	Mylar Tape																					
15	Lead wire	Lead wire Diameter 0.8mm																					
Other																							
8			7			6			5			4			3			2			1		