

MESSRS.

SPECIFICATION FOR APPROVAL**承 认 书**

Product	ELECTRET CONDENSER MICROPHONE
Part No.	HMB-O40J42-CWH10(RoHS)
Customer Part No.	
Customer Approval	

Approved By	Checked By	Made By
王台平 AUG-20-2018	曹丽萍 AUG-20-2018	LILY AUG-20-2018

常 州 华 龙 电 子 有 限 公 司
DRAGONSTATE ELECTRONIC CORPORATION

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

1. 变更记录 (History change record)

Change Items	Date	Note	Drawn by	Checked by
	2018-08-20	First Issue	Lily 2018-08-20	王台平 2018-08-20
增加阻抗下限值 标注	2018-11-30	Second Issue	Lily 2018-11-30	王台平 2018-11-30

2. 储藏与判断条件 (Storage And Judgement Conditions)

	Temperature Range(°C)	Rel. Humidity(%)	Static Pressure(kPa)
Judgement	19~21	60~70	86~106
Storage	-25~70		
Operating	-25~70		


3. 规格 (Specifications)

Test conditions($V_S=2.0V$ $R_L=2.2k\Omega$ $Temp=20\pm 2^{\circ}C$ $R.H=60\pm 5\%$)


Item	Symbol	Test Conditions	Min	Standard	Max	Unit
灵敏度 Sensitivity	S	$f=1kHz, P_{in}=1Pa$	-45	-42	-39	dB ($0dB=1V/Pa$)
阻抗 Impedance	Z	$f=1kHz, P_{in}=1Pa$	0.7		2.2	$k\Omega$
指向性 Directivity		Omni-directional				
消耗电流 Current Consumption	I				500	μA
工作电压 Operation Voltage Range	U		1.0	2.0	10	V
信噪比 S/N Ratio	S/N(A)	$f=1kHz, P_{in}=1Pa$ A Curve	58			dB
降压特性 Decreasing Voltage Characteristic	ΔS	$f=1kHz, P_{in}=1Pa$ $V_S=2.0-1.5V$			-3	dB
最大输入声压级 Max.Input Sound Level	MISPL	$f=1kHz$ Distortion<1%			110	dB

4. 测试电路 (Standard Test Circuit)


$V_S=2.0V$ $R_L=2.2k\Omega$ $T_e=20^{\circ}C$ $R.H.=60\%$




5. 测试装备图（Standard Test Fixture）




6 频响曲线（Frequency Response Curve）



7.外观图 (Appearance Drawing)



8. 材料及结构清单 (List and Structure of Materials)



No. 序号	Part name 部件名称	Material Type 材料型号	Qty 数量	Origin 产地	Manufactur e 协力厂商	Remarks 备注
1	PCB	Epoxy FR-4	1	Hongkon g	Jiantao	
2	Cavity	POM	1	Japan	Suzhou	
3	Copper ring	Brass AT65	1	China	Suzhou	
4	Back plate	ALSET FC-CNZ	1	Korea	3A	
5	Cushion plate	Mylar	1	China	Hebei	
6	Diaphragm	PPS	1	Japan	Dongli	
7	Case	Magal	1	China	Shanghai	
8	Cloth	non-woven fabrics	1	Japan	Sanjing	
9	Lead wire	UL1571 AWG 32	1	China	Shanghai	Red+
10	Lead wire	UL1571 AWG 32	1	China	Shanghai	Black-
11	Capacitor	10pF 0402	1	Japan	Murata	
12	Capacitor	33pF 0402	1	Japan	Murata	
13	FET	TF252THC	1	Japan	Sanyo	

9. 可靠性试验 (Reliability Test)

在下列试验完成后,在温度为 20℃,相对湿度为 65%的条件下恢复 3 小时后进行测试,灵敏度与初始灵敏度相差在±3dB 以内.

(All tests should be done after 3 hours of conditioning at 20℃, R.H65%, while the sensitivity is to be within ±3dB, from the initial sensitivity after the following experiments.)

9.1 高温试验 (HIGH TEMPERATURE TEST)

温度(High temperature): +70℃

放置时间(Duration): 240hours

9.2 低温试验 (LOW TEMPERATURE TEST)

温度(Low temperature): -30℃

放置时间(Duration): 240 hours

9.3 温度循环试验(如图 1) (TEMPERATURE CYCLE TEST) (See in Fig.1)

低温(Low temperature): -30℃

高温(High temperature): +70℃

转化时间(Changeover time): 10min

放置时间(Duration): 30min

次数(Cycle): 5

9.4 湿度 (STATIC HUMIDITY TEST)

温度(Temperature): +50℃

相对湿度(Relative humidity): 90 ~ 95%

放置时间(Duration): 200 hours

9.5 振动试验 (VIBRATION TEST)

振幅(Amplitude): 1.52mm

持续时间(Duration): 1 分钟/面(minutes/plane)

频度范围(Freq.range): 10 ~ 55Hz

试验时间(Total time): 2 小时(hour)

9.6 跌落试验 (DROP TEST)

不带包装的跌落到 20mm 厚的地板上(Drop a unit unpacked onto a board of 20mm thick)

高度(Height): 1 m

次数(Cycle): 6 (1 each plane)

10. 焊接要求 (Regarding the Soldering operation)


每个驻极体电容传声器在其麦克风上都有一个 FET,这种 FET 在过热和电流撞击时易损坏，所以对于焊接应遵循以下操作：

- 要求使用 25W-35W 烙铁，并保持 $350\pm 10^{\circ}\text{C}$ 的温度范围。
- 在每一个端的焊接应在 2 秒内完成，以防过热。
- 禁止单体麦克风焊接。（否则会影响驻极体电容传声器的灵敏度）
- 最理想的散热装置按以下设计。


Every ECM contains a FET with microphone body.

This FET easy to damageable from excessive heat and electrical shock. Proper attention for the soldering work is required same as followings.

- Recommend to use 25W-35W ceramic soldering iron and apply $350\pm 10^{\circ}\text{C}$ temperature range
- Soldering should be accomplished within 2 seconds at each terminal so as not to be overheated.
- Do not make a cavity at the surface of lead lump on the PCB. wiring board.
(Opened cavity will influence to the sensitivity of ECM)
- Optimal design for heat sink pad is same as below.



11. 包装规格 (Packing Specifications)

REV NO.	REVISION NOTE	APPROVAL	DATE
			
100pcs per plastic bag NW:15g GW:20g MODEL: QTY:50PCS LOT NO: 1000pcs per plastic box NW:300g GW:450g MODEL: QTY:1000PCS LOT NO: 10000pcs per out bag NW:3.0KG GW:5.5KG MODEL: QTY:10000PCS LOT NO:			
TITLE: packing		DRAWN: Lily 2009/05/23 SCALE: 5/1 SHEET: 1 : 1	
PART NO.		DESIGNED: R & D OF D.S. UNITS: mm	
DWG NO.		CHECKED: Emily TOLERANCE ± 0.2	
REV 1		APPROVAL: Eric UNLESS OTHERWISE SPECIFIED:	
MATERIAL: *****		ONE PLACE DECIMAL ± ***	
		TWO PLACE DECIMAL ± ***	
		THREE PLACE DECIMAL ± ***	
DS DRAGONSTATE ELECTRONIC CORPORATION			