

1.Description

The 74AUP2G34 is a high performance dual buffer operating from a 0.8 to 3.6V supply. This device is fabricated with advanced CMOS technology to achieve ultra-high speed with high output drive.

2.Features

- Designed for 0.8V to 3.6V V_{CC} Operation
- Low static power consumption; $I_{CC}=0.7\mu A$ (maximum)
- 4mA Balanced Output Sink and Source Capability
- Near Zero Static Supply Current Substantially Reduces System Power Requirements
- These Devices are Pb-Free and are RoHS Compliant

3.Pinning information




Figure1. Top View



4.Pin Function

Pin No.		Function
SC70-6/SOT23-6	DFN6	
1	1	A1
2	2	GND
3	3	A2
4	4	Y2
5	5	VCC
6	6	Y1



5.Block Diagram




Figure2.

Function Table

Input	Output
A	Y
H	H
L	L



6. Absolute Maximum Ratings

Parameter		Symbol	Value	Units
DC Supply Voltage		V_{CC}	-0.5 to 4.6	V
DC Input Voltage		V_I	$-0.5 \leq V_I \leq 4.6$	V
DC Output Voltage Output in Higher or Low State ⁽¹⁾		V_O	-0.5 to 4.6	V
DC Input Diode Current $V_I < GND$		I_{IK}	-50	mA
DC Output Diode Current $V_O < GND, V_O > V_{CC}$		I_{OK}	± 50	mA
DC Output Sink Current		I_O	± 20	mA
DC Supply Current per Supply Pin		I_{CC}	± 50	mA
Storage Temperature Range		T_{STG}	-65 to 150	°C
Lead Temperature, 1 mm from Case for 10 Seconds		T_L	260	°C
Junction Temperature Under Bias		T_J	150	°C
Power Dissipation in Still Air at 85°C		P_D	200	mW
ESD Classification	Human Body Model	V_{ESD}	± 4000	V
	Machine Model		± 200	V
	Charged Device Model		± 1000	V
Latchup Current Above V_{CC} and GND at 125°C		I_{LU}	± 100	mA

7. Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
DC Supply Voltage Operating	V_{CC}	0.8	3.6	V
DC input Voltage	V_{IN}	0	3.6	V
DC Output Voltage (High or Low State)	V_{OUT}	0	3.6	V
Operating Temperature Range	T_A	-40	85	°C

Notes:

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied.



8. Electrical Characteristics

DC Electrical Characteristics

Parameter	Condition	Symbol	$V_{CC}(V)$	$T_A=25^{\circ}C$			$-40^{\circ}C \leq T_A \leq 85^{\circ}C$		Units
				Min	Typ	Max	Min	Max	
High-Level Input Voltage		V_{IH}	0.8	$0.75V_{CC}$			$0.75V_{CC}$		V
			0.9 to 1.95	$0.7V_{CC}$			$0.7V_{CC}$		
			2.3 to 2.7	1.6			1.6		
			3 to 3.6	2			2		
Low-Level Input Voltage		V_{IL}	0.8			$0.25V_{CC}$		$0.25V_{CC}$	V
			0.9 to 1.95			$0.3V_{CC}$		$0.3V_{CC}$	
			2.3 to 2.7			0.7		0.7	
			3.0 to 3.6			0.9		0.9	
High-Level Output Voltage	$I_{OH}=-20\mu A$	V_{OH}	0.8 to 3.6	$V_{CC}-0.1$			$V_{CC}-0.1$		V
	$I_{OH}=-1.1mA$		1.1	0.82	1.02		0.77		
	$I_{OH}=-1.7\mu A$		1.4	1.11	1.32		1.03		
	$I_{OH}=-1.9mA$		1.65	1.32	1.58		1.30		
	$I_{OH}=-2.3mA$		2.3	2.05	2.24		1.97		
	$I_{OH}=-3.1mA$			1.9	2.22		1.85		
	$I_{OH}=-2.7mA$		3	2.72	2.95		2.67		
	$I_{OH}=-4.0mA$			2.6	2.92		2.55		
Low-Level Output Voltage	$I_{OL}=20\mu A$	V_{OL}	0.8 to 3.6			0.1		0.1	V
	$I_{OL}=1.1mA$		1.1		0.11	0.33		0.33	
	$I_{OL}=1.7mA$		1.4		0.12	0.31		0.37	
	$I_{OL}=1.9mA$		1.65		0.11	0.31		0.35	
	$I_{OL}=2.3mA$		2.3		0.14	0.31		0.33	
	$I_{OL}=3.1mA$				0.19	0.44		0.45	
	$I_{OL}=2.7mA$		3		0.11	0.31		0.33	
	$I_{OL}=4.0mA$				0.16	0.44		0.45	



Input Leakage Current	$V_{IN}=V_{CC}$ or GND	I_{IN}	0 to 3.6			0.1		0.2	μA
Power Off Leakage Current	$V_{IN}=3.6V$ or $V_{OUT}=3.6V$	I_{OFF}	0			0.2		0.5	μA
Quiescent Supply Current	$V_{IN}=3.6V$ or GND	I_{CC}	3.6			0.2		0.7	μA



9.AC Electrical Characteristics

$t_r = t_f = 2.5\text{ns}$

Parameter	Condition	Symbol	V _{CC} (V)	T _A =25°C			-40°C≤T _A ≤85°C		Units
				Min	Typ	Max	Min	Max	
Propagation Delay (Figure3 And 4)	C _L =5pF ⁽⁶⁾	t _{PHL}	0.8		18				ns
			1.2	2.6	7.3	12.8	2.1	15.6	
			1.5	1.4	5.2	8.7	0.9	10.3	
			1.8	1	4.2	6.6	0.5	8.2	
			2.5	1	3	4.4	0.5	5.5	
			3.3	1	2.4	3.5	0.5	4.3	
	C _L =10pF ⁽⁶⁾		0.8		21				ns
			1.2	1.5	8.5	14.7	1	17.2	
			1.5	1	6.2	10	0.5	11.3	
			1.8	1	5	7.7	0.5	9	
			2.5	1	3.6	5.2	0.5	6.1	
			3.3	1	2.9	4.2	0.5	4.7	
	C _L =15pF ⁽⁶⁾	t _{PLH}	0.8		24				ns
			1.2	3.6	9.9	16.3	3.1	19.9	
			1.5	2.3	7.2	11.1	1.8	13.2	
			1.8	1.6	5.8	8.7	1.1	10.6	
			2.5	1	4.3	5.9	0.5	7.3	
			3.3	1	3.4	4.8	0.5	5.9	
	C _L =30pF ⁽⁶⁾		0.8		32.8				ns
			1.2	4.9	13.1	20.9	4.4	25.5	
			1.5	3.4	9.5	14.2	2.9	16.9	
			1.8	2.5	7.7	11	2	13.5	
			2.5	1.8	5.7	7.6	1.3	9.4	
			3.3	1.5	4.7	6.2	1	7.5	

Notes: (6) C_L includes probe and jig capacitance.



10.Capacitance Characteristics

Parameter	Symbol	Condition		Typ	Units
Input Capacitance	C_{IN}	$V_{CC}=3.6V$, $V_I=0V$ or V_{CC}		2	pF
output capacitance	C_O	$V_{CC}=0V$, $V_{OUT}=GND$		3	pF
Power Dissipation Capacitance ⁽⁷⁾	C_{PD}	1MHz, $V_I=0V$ to V_{CC}	$V_{CC}=0.8V$	4	pF
			$V_{CC}=1.2V$	4	
			$V_{CC}=1.5V$	4	
			$V_{CC}=1.8V$	4	
			$V_{CC}=2.5V$	4.1	
			$V_{CC}=3.3V$	4.3	

Notes:

(7) C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.



11.AC Test Circuit




Figure 3. Switching Waveforms





Figure 4. Test Circuit



12.1SC70-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	L1
Min	0.90	0.00	0.90	0.15	0.08	2.05	2.15	1.15	0.65	1.2	0.26	0.525
Max	1.10	0.10	1.00	0.35	0.15	2.25	2.45	1.35	TYP.	1.4	0.46	REF.

Symbol	θ
Min	0°
Max	8°



12.2SOT23-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



12.3DFN6(1*1.5) Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A3	b	D	E	e	H	L	L1
Min	0.50	0	0.10	0.15	0.90	1.40	0.40	0.10	0.30	0.35
Max	0.60	0.05	REF	0.25	1.10	1.60	0.60	REF	0.40	0.45



13.Ordering information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SN74AUP2G34DBVR	PZ	SOT23-6	3000	Tape and reel
UMW SN74AUP2G34DCKR	PZ5	SC70-6	3000	Tape and reel
UMW SN74AUP2G34DRYR	PZ	DFN6	5000	Tape and reel



14.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.