


**SMB General Purpose Rectifier Diode 通用整流二极管**

■ **Features 特点**

Glass passivated junction 玻璃钝化结  
Low reverse leakage current 低反向漏电流  
Low forward voltage drop 低正向压降  
High current capability 高电流能力  
Surface mount device 表面贴装器件  
Case 封装:SMB(DO-214AA)



**HF** **RoHS**



■ **Maximum Rating 最大额定值**

( $T_A=25^{\circ}\text{C}$  unless otherwise noted 如无特殊说明, 温度为  $25^{\circ}\text{C}$ )

Characteristic 特性参数	Symbol 符号	S5AB -6AF	S5BB -6AF	S5DB -6AF	S5GB -6AF	S5JB -6AF	S5KB -6AF	S5MB -6AF	Unit 单位
Marking 印字		S5A	S5B	S5D	S5G	S5J	S5K	S5M	
Peak Reverse Voltage 反向峰值电压	$V_{RRM}$	50	100	200	400	600	800	1000	V
DC Reverse Voltage 直流反向电压	$V_R$	50	100	200	400	600	800	1000	V
RMS Reverse Voltage RMS 反向电压	$V_{R(RMS)}$	35	70	140	280	420	560	700	V
Forward Rectified Current 正向整流电流	$I_F$	5							A
Peak Surge Current 峰值浪涌电流	$I_{FSM}$	120							A
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	13							$^{\circ}\text{C}/\text{W}$
Junction and Storage Temperature 结温和储藏温度	$T_J, T_{stg}$	$150^{\circ}\text{C}, -55\text{to}+150^{\circ}\text{C}$							

■ **Electrical Characteristics 电特性**

( $T_A=25^{\circ}\text{C}$  unless otherwise noted 如无特殊说明, 温度为  $25^{\circ}\text{C}$ )

Characteristic 特性参数	Symbol 符号	Min 最小值	Typ 典型值	Max 最大值	Unit 单位	Condition 条件
Forward Voltage 正向电压	$V_F$		1.0	1.1	V	$I_F=5\text{A}$
Reverse Current 反向电流	$I_R$		( $T_A=25^{\circ}\text{C}$ ) ( $T_A=125^{\circ}\text{C}$ )	5 250	$\mu\text{A}$	$V_R=V_{RRM}$
Diode Capacitance 二极管电容	$C_D$		60		pF	$V_R=4\text{V}, f=1\text{MHz}$

■ Typical Characteristic Curve 典型特性曲线

FIG.1-TYPICAL FORWARD CHARACTERISTICS




FIG.2-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3 - TYPICAL REVERSE CHARACTERISTICS






FIG.5-TYPICAL JUNCTION CAPACITANCE



■ Dimension 外形封装尺寸

**DO-214AA(SMB)**



Dimensions in inches and (millimeters)