


## 1.Description

The UMW SN74LVC1G07 is a high performance single non-inverting buffer with open drain outputs operating from a 1.65 to 5.5V supply. The Output stage is open drain with Over Voltage Tolerance. This allows the SN74LVC1G07 to be used to interface 5.0V circuits to circuits of any voltage between 0 and +7.0V.


## 2.Features

- Tiny SC70-5, SOT23-5 and DFN6-1.0mm\*1.5mm Packages
- Designed for 1.65V to 5.5V  $V_{CC}$  Operation  
24mA Output Sink Capability, Pullup may be
- between 0 and 7.0V
- Near Zero Static Supply Current Substantially Reduces System Power Requirements
- These Devices are Pb-Free and RoHS Compliant

## 3.Pinning information



**SOT23-5/SC70-5**



**DFN6**

Figure1. Top View



4.Pin Function

SC70-5/ SOT23-5

| Pin | Function |
|-----|----------|
| 1   | NC       |
| 2   | INA      |
| 3   | GND      |
| 4   | OUT      |
| 5   | VCC      |

DFN6

| Pin | Function |
|-----|----------|
| 1   | NC       |
| 2   | INA      |
| 3   | GND      |
| 4   | OUT      |
| 5   | NC       |
| 6   | VCC      |



5.Block Diagram




Figure2. Logic Symbol

Function Table

| Input | Output |
|-------|--------|
| A     | Y      |
| L     | L      |
| H     | Z      |



## 6. Absolute Maximum Ratings

| Parameter                                                          |                               | Symbol        | Value                  | Units |
|--------------------------------------------------------------------|-------------------------------|---------------|------------------------|-------|
| DC Supply Voltage                                                  |                               | $V_{CC}$      | -0.5 to 7              | V     |
| DC Input Voltage                                                   |                               | $V_I$         | $-0.5 \leq V_I \leq 7$ | V     |
| DC Output Voltage Output in Higher or Low State (Note 1)           |                               | $V_O$         | -0.5 to $V_{CC} + 0.5$ | V     |
| DC Input Diode Current $V_I < GND$                                 |                               | $I_{IK}$      | -50                    | mA    |
| DC Output Diode Current $V_O < GND, V_O > V_{CC}$                  |                               | $I_{OK}$      | $\pm 50$               | mA    |
| DC Output Sink Current                                             |                               | $I_O$         | $\pm 50$               | mA    |
| DC Supply Current per Supply Pin                                   |                               | $I_{CC}$      | $\pm 100$              | mA    |
| Storage Temperature Range                                          |                               | $T_{STG}$     | -65 to 150             | °C    |
| Lead Temperature, 1 mm from Case for 10 Seconds                    |                               | $T_L$         | 260                    | °C    |
| Junction Temperature Under Bias                                    |                               | $T_J$         | 150                    | °C    |
| Thermal Resistance                                                 | SC70-6                        | $\theta_{JA}$ | 333                    | °C/W  |
|                                                                    | SOT23-6                       |               | 225                    | °C/W  |
|                                                                    | DFN6                          |               | 423                    | °C/W  |
| Power Dissipation in Still Air at 85°C                             |                               | $P_D$         | 200                    | mW    |
| Moisture Sensitivity                                               |                               | MSL           | Level 1                |       |
| ESD Classification Human                                           | Body Model (Note 2)           | $V_{ESD}$     | 2000                   | V     |
|                                                                    | Machine Model (Note3)         |               | 200                    | V     |
|                                                                    | Charged Device Model (Note 4) |               | N/A                    | V     |
| Latchup Performance Above $V_{CC}$ and Below GND at 125°C (Note 5) |                               | $I_{Latchup}$ | $\pm 100$              | mA    |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. IO absolute maximum rating must be observed.
2. Tested to EIA/JESD22—A114—A, rated to EIA/JESD22—A114—B.
3. Tested to EIA/JESD22—A115—A, rated to EIA/JESD22—A115—A.
4. Tested to JESD22—C101—A.
5. Tested to EIA/JESD78.



## 7. Recommended Operating Conditions

| Parameter                             |                              | Symbol                          | Min  | Max | Unit |
|---------------------------------------|------------------------------|---------------------------------|------|-----|------|
| DC Supply Voltage Operating           |                              | V <sub>CC</sub>                 | 1.65 | 5.5 | V    |
| Data Retention                        |                              |                                 | 1.5  | 5.5 | V    |
| DC Input Voltage                      |                              | V <sub>IN</sub>                 | 0    | 5.5 | V    |
| DC Output Voltage (High or Low State) |                              | V <sub>OUT</sub>                | 0    | 5.5 | V    |
| Operating Temperature Range           |                              | T <sub>A</sub>                  | -40  | 85  | °C   |
| Input Rise and Fall Time              | V <sub>CC</sub> =2.5V ± 0.2V | t <sub>r</sub> , t <sub>f</sub> | 0    | 20  | ns/V |
|                                       | V <sub>CC</sub> =3V ± 0.3V   |                                 | 0    | 10  | ns/V |
|                                       | V <sub>CC</sub> =5V ± 0.5V   |                                 | 0    | 5   | ns/V |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied.



## 8.DC Electrical Characteristics

| Parameter                                                 | Condition                                       | Symbol           | V <sub>CC</sub> (V) | T <sub>A</sub> =25°C |      |                     | -40°C≤T <sub>A</sub> ≤85°C |                     | Units |
|-----------------------------------------------------------|-------------------------------------------------|------------------|---------------------|----------------------|------|---------------------|----------------------------|---------------------|-------|
|                                                           |                                                 |                  |                     | Min                  | Typ  | Max                 | Min                        | Max                 |       |
| High-Level Input Voltage                                  |                                                 | V <sub>IH</sub>  | 1.65 to 1.95        | 0.75V <sub>CC</sub>  |      |                     | 0.75V <sub>CC</sub>        |                     | V     |
|                                                           |                                                 |                  | 2.3 to 5.5          | 0.7V <sub>CC</sub>   |      |                     | 0.7V <sub>CC</sub>         |                     |       |
| Low-Level Input Voltage                                   |                                                 | V <sub>IL</sub>  | 1.65 to 1.95        |                      |      | 0.25V <sub>CC</sub> |                            | 0.25V <sub>CC</sub> | V     |
|                                                           |                                                 |                  | 2.3 to 5.5          |                      |      | 0.3V <sub>CC</sub>  |                            | 0.3V <sub>CC</sub>  |       |
| Low-Level Output Voltage V <sub>IN</sub> =V <sub>IL</sub> | I <sub>OL</sub> =100μA                          | V <sub>OL</sub>  | 1.65 to 5.5         |                      | 0.0  | 0.1                 |                            | 0.1                 | V     |
|                                                           | I <sub>OL</sub> =3mA                            |                  | 1.65                |                      | 0.08 | 0.24                |                            | 0.24                |       |
|                                                           | I <sub>OL</sub> =8mA                            |                  | 2.3                 |                      | 0.2  | 0.3                 |                            | 0.3                 |       |
|                                                           | I <sub>OL</sub> =12mA                           |                  | 2.7                 |                      | 0.22 | 0.4                 |                            | 0.4                 |       |
|                                                           | I <sub>OL</sub> =16mA                           |                  | 3                   |                      | 0.28 | 0.4                 |                            | 0.4                 |       |
|                                                           | I <sub>OL</sub> =24mA                           |                  | 3                   |                      | 0.38 | 0.55                |                            | 0.55                |       |
|                                                           | I <sub>OL</sub> =32mA                           |                  | 4.5                 |                      | 0.42 | 0.55                |                            | 0.55                |       |
| Input Leakage Current                                     | V <sub>IN</sub> =5.5V or GND                    | I <sub>IN</sub>  | 0 to 5.5            |                      |      | ±0.1                |                            | ±1                  | μA    |
| Power Off Leakage Current                                 | V <sub>IN</sub> =5.5V or V <sub>OUT</sub> =5.5V | I <sub>OFF</sub> | 0                   |                      |      | 1                   |                            | 10                  | μA    |
| Quiescent Supply Current                                  | V <sub>IN</sub> =5.5V or GND                    | I <sub>CC</sub>  | 5.5                 |                      |      | 1                   |                            | 10                  | μA    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.



## 9.AC Electrical Characteristics

| Parameter                             | Condition                                  | Symbol           | V <sub>CC</sub> (V) | T <sub>A</sub> =25°C |     |      | -40°C≤T <sub>A</sub> ≤85°C |      | Units |
|---------------------------------------|--------------------------------------------|------------------|---------------------|----------------------|-----|------|----------------------------|------|-------|
|                                       |                                            |                  |                     | Min                  | Typ | Max  | Min                        | Max  |       |
| Propagation Delay<br>(Figure 3 and 4) | R <sub>L</sub> =500Ω, C <sub>L</sub> =15pF | t <sub>PZL</sub> | 1.8                 | 2                    | 9.1 | 11.1 | 2                          | 12.8 | ns    |
|                                       |                                            |                  | 2.5                 | 1.5                  | 6.1 | 7.5  | 1.5                        | 8.5  |       |
|                                       |                                            |                  | 3.3                 | 1.2                  | 4.9 | 6    | 1.5                        | 6.9  |       |
|                                       |                                            |                  | 5                   | 0.8                  | 3.9 | 4.9  | 0.8                        | 5.5  |       |
| Propagation Delay<br>(Figure 3 and 4) | R <sub>L</sub> =500Ω, C <sub>L</sub> =15pF | t <sub>PLZ</sub> | 1.8                 | 2                    | 9.1 | 11.1 | 2                          | 12.8 |       |
|                                       |                                            |                  | 2.5                 | 1.5                  | 5.9 | 7.3  | 1.5                        | 8.3  |       |
|                                       |                                            |                  | 3.3                 | 1.2                  | 3.9 | 4.9  | 1.5                        | 5.5  |       |
|                                       |                                            |                  | 5                   | 0.8                  | 3   | 3.7  | 0.8                        | 4.2  |       |

## 10.Capacitance Characteristics


| Parameter                                    | Symbol          | Condition                                                           | Typ  | Units |
|----------------------------------------------|-----------------|---------------------------------------------------------------------|------|-------|
| Input Capacitance                            | C <sub>IN</sub> | V <sub>CC</sub> =5.5V, V <sub>I</sub> = 0V or V <sub>CC</sub>       | >2.5 | pF    |
| Power Dissipation Capacitance <sup>(6)</sup> | C <sub>PD</sub> | 10MHz, V <sub>CC</sub> =3.3V, V <sub>I</sub> =0V or V <sub>CC</sub> | 26   | pF    |
|                                              |                 | 10MHz, V <sub>CC</sub> =5.5V, V <sub>I</sub> =0V or V <sub>CC</sub> | 30   | pF    |

Notes 6:

C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC(OPR)</sub>=C<sub>PD</sub>\*V<sub>CC</sub>\*f<sub>in</sub>+I<sub>CC</sub>\*C<sub>PD</sub> is used to determine the no-load dynamic power consumption; P<sub>D</sub>=C<sub>PD</sub>\*V<sub>CC</sub><sup>2</sup>\*f<sub>in</sub>+I<sub>CC</sub>\*V<sub>CC</sub>\*Fig.



## 11.1 SC70-5 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

| Symbol | A    | A1   | A2   | b    | c    | D    | E    | E1   | e    | e1   | L    | θ    |
|--------|------|------|------|------|------|------|------|------|------|------|------|------|
| Min    | 0.90 | 0.00 | 0.90 | 0.15 | 0.08 | 2.05 | 1.15 | 2.15 | 0.65 | 1.20 | 0.26 | 7°   |
| Max    | 1.10 | 0.10 | 1.00 | 0.35 | 0.15 | 2.25 | 1.35 | 2.45 | TYP  | 1.40 | 0.46 | REF. |





11.2 SOT-23-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A     | A1    | A2    | b     | c     | D     | E1    | E     | e     | e1    | L     | $\theta$ |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|----------|
| Min    | 1.050 | 0.000 | 1.050 | 0.300 | 0.100 | 2.820 | 1.500 | 2.650 | 0.950 | 1.800 | 0.300 | 0°       |
| Max    | 1.250 | 0.100 | 1.150 | 0.500 | 0.200 | 3.020 | 1.700 | 2.950 | BSC   | 2.000 | 0.600 | 8°       |



11.3 DFN6(1\*1.5) Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A    | A1   | A3   | b    | D    | E    | e    | H    | L    | L1   |
|--------|------|------|------|------|------|------|------|------|------|------|
| Min    | 0.50 | 0    | 0.10 | 0.15 | 0.90 | 1.40 | 0.40 | 0.10 | 0.30 | 0.35 |
| Max    | 0.60 | 0.05 | REF  | 0.25 | 1.10 | 1.60 | 0.60 | REF  | 0.40 | 0.45 |



12.Ordering information



yww: Batch Code

| Order Code          | Marking | Package | Base QTY | Delivery Mode |
|---------------------|---------|---------|----------|---------------|
| UMW SN74LVC1G07DBVR | C075    | SOT23-5 | 3000     | Tape and reel |
| UMW SN74LVC1G07DCKR | CV5     | SC70-5  | 3000     | Tape and reel |
| UMW SN74LVC1G07DRYR | CV      | DFN6    | 5000     | Tape and reel |



## **13.Disclaimer**

---

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.