

1. Description

UMW TC4424AVOA713 is power switch driver. It has a matching rise and fall time when charging and discharging the gate of the power switch. UMW TC4424AVOA713 has high latch resistance under all conditions in its rated power and voltage range. When noise spikes of up to 5V (either polarity) occur on the ground pin, the UMW TC4424AVOA713 is not damaged. UMW TC4424AVOA713 can accept reverse currents up to 500mA to force back its output without damage or logic confusion. All ports are fully protected by up to 2.0 kV electrostatic discharge (ESD).

3. Features


- Latch Protection: withstand 0.5 A reverse current
- Ability to Handle Negative Voltages (-10 V) at Inputs
- Low Output Impedance
- Two Independent Gate-Drive Channel
- 4-A Peak Output Current
- 4.5 to 25-V Single-Supply Range
- High Ability of driving capacitive load
- Rise/Fall time matching
- Operating Temperature Range of -40 to 125°C
- Turn on/Turn off Delays:
 - -- Ton/Toff = 25ns/25ns

2. Applications

- Switch-Mode Power Supplies
- line drivers
- Pulse transformer driver
- Driving MOSFETs and IGBTs
- Motor drives
- Pulse generator
- Switch-Mode Power Supplies
- DC-to-DC Converters
- Class D switching amplifier




4. Pin Configuration





5. Pinning Information



SOP-8

Lead Definitions

Number	Symbol	Description
1	NC	
2	INA	Input to Channel A
3	GND	Ground: All signals are referenced to this pin
4	INB	Input to Channel B
5	OUTB	Output of Channel B
6	V _{cc}	Bias supply input
7	OUTA	Output of Channel A
8	NC	



6. Absolute Maximum Ratings

Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. All voltages are with respect to GND unless otherwise noted. Currents are positive into, negative out of the specified terminal, environment temperature is 25°C.

Parameter	Symbol	Min	Max	Units
Supply voltage range	V _{CC}		25	V
INA, INB voltage	V _{IN}	GND-10	V _{CC} +0.3	V
Human body model (HBM)	ESD		2000	V
Charged device model (CDM)			500	V
SOIC package power (T _A ≤ 70°C)	P _D		470	mW
Operating junction temperature	T _J		+150	°C
Storage temperature	T _S	-45	+150	°C



7. Electrical Characteristics

$T_A=25^\circ\text{C}$, $V_{CC}=15\text{V}$ (unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Units
Input signal high threshold	V_{IH}		2.4			V
Input signal low threshold	V_{IL}				0.8	V
Input current	I_{IN+}	$V_{IN}=5\text{V}$		50		μA
Input current	I_{IN-}	$V_{IN}=0\text{V}$			1	μA
High output voltage	V_{OH}				$V_{CC}-0.025$	V
Low output voltage	V_{OL}				0.025	V
Output pullup resistance	R_{OH}	$I_O=100\text{mA}$		0.7		Ω
Output pulldown resistance	R_{OL}	$I_O=100\text{mA}$		0.4		Ω
Peak output source current	I_{PK}			4		A
Reverse current that latch protection can withstand (Working cycle $\leq 2\%$, $t \leq 300\text{us}$)	I_{REV}				>0.5	A
Rise time	t_R	$C_{LOAD}=1800\text{pF}$			10	ns
Fall time	t_F	$C_{LOAD}=1800\text{pF}$			10	ns
Turn-on propagation delay	t_{ON}	$C_{LOAD}=1800\text{pF}$		25	35	ns
Turn-off propagation delay	t_{OFF}	$C_{LOAD}=1800\text{pF}$		25	35	ns
V_{CC} quiescent supply current	I_{Q1}	$V_{INA}=V_{INB}=\text{HIGH}$			1	mA
V_{CC} quiescent supply current	I_{Q0}	$V_{INA}=V_{INB}=\text{LOW}$			1	mA

8.Detailed Description





Figure 1. Input-Output waveform(non-inverting)

9. Functional Block Diagram





10.Typical Application





Figure 2. Typical Application Diagram of UMW TC4424AVOA713

11. SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	L	θ
Min	1.350	0.000	1.350	0.330	0.170	4.700	3.800	5.800	1.270	0.400	0°
Max	1.750	0.100	1.550	0.510	0.250	5.100	4.000	6.200	BSC	1.270	8°



12.Ordering information



yy: Year Code

ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW TC4424AVOA713	SOP-8	2500	Tape and reel



13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.