


1.Features

- $V_{DS(V)} = -30V$
- $I_D = -50A$
- $R_{DS(ON)} < 10.5m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 18m\Omega (V_{GS} = -4.5V)$
- Logic Level-Enhancement mode
- AEC qualified
- 175°C operating temperature
- Green Product (RoHS compliant)
- Intended for reverse battery protection

2.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



3.Absolute Maximum Ratings $T_J = 25^\circ C$

Parameter	Symbol	Conditions	Value	Units
Continuous drain current	I_D	$T_C = 25^\circ C, V_{GS} = -10V^{(1)}$	-50	A
		$T_C = 100^\circ C, V_{GS} = -10V^{(2)}$	-42	A
Pulsed drain current ²⁾	$I_{D,pulse}$	$T_C = 25^\circ C$	-200	A
Avalanche energy, single pulse	E_{AS}	$I_D = -25A$	100	mJ
Avalanche current, single pulse	I_{AS}		-50	A
Gate source voltage	V_{GS}		-16 to 5	V
Power dissipation	P_{tot}	$T_C = 25^\circ C$	58	W
Storage temperature	T_J, T_{STG}		-55 to 175	°C
IEC cimatic category; DIN IEC 68-1			55/175/56	



4. Electrical Characteristic ($T_J=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Thermal resistance, junction -case	R_{thJC}				2.6	K/W
SMD version, device on PCB	R_{thJA}	minimal footprint			62	K/W
		6 cm ² cooling area ³⁾			40	K/W
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=-1mA$	-30			V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-85\mu A$	-1	-1.5	-2	V
Zero gate voltage drain current	I_{DSS}	$V_{DS}=-24V, V_{GS}=0V, T_J=25^\circ\text{C}$		-0.02	-1	μA
		$V_{DS}=-24V, V_{GS}=0V, T_J=125^\circ\text{C}^{2)}$		-7	-70	μA
Gate-source leakage current	I_{GSS}	$V_{GS}=-16V, V_{DS}=0V$			-100	nA
Drain-source on-state resistance ⁵⁾	$R_{DS(ON)}$	$V_{GS}=-4.5V, I_D=-25A$		13	18	m Ω
		$V_{GS}=-10V, I_D=-50A$		8.3	10.5	m Ω
Input capacitance	C_{iss}	$V_{GS}=0V, V_{DS}=-25V, f=1MHz$		2900		pF
Output capacitance	C_{oss}			835	3770	pF
Reverse transfer capacitance	C_{rss}			21	1090	pF
Turn-on delay time	$t_{D(on)}$	$V_{DD}=-15V, V_{GS}=-10V$ $I_D=-50A, R_G=3.5\Omega$		7	42	ns
Rise time	t_r			3		ns
Turn-off delay time	$t_{D(off)}$			45		ns
Fall time	t_f			14		ns
Gate to source charge	Q_{gs}	$V_{DD}=-24V, I_D=-50A$ $V_{GS}=0 \text{ to } -10V$		11	14	nC
Gate to drain charge	Q_{gd}			5	10	nC
Gate charge total	Q_g			42	55	nC
Gate plateau voltage	$V_{plateau}$			-3.6		V
Diode continuous forward current ²⁾	I_S	$T_C=25^\circ\text{C}$			-50	A
Diode pulse current ²⁾	$I_{S,pulse}$				-200	A




Diode forward voltage	V_{SD}	$V_{GS}=0V, I_F=-50A, T_J=25^{\circ}C$		-1	-1.3	V
Reverse recovery time ²⁾	t_{rr}	$V_R=-15V, I_F=40A, di_F/dt=-100A/\mu s$		35		ns
Reverse recovery charge ²⁾	Q_{rr}			26		nC

Notes:

- ¹⁾ Current is limited by bondwire; with an $R_{thJC} = 2.6K/W$ the chip is able to carry 60A at 25°C.
- ³⁾ Specified by design. Not subject to production test.
- ⁵⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection.
PCB is vertical in still air.




5.1Typical characteristic






5.2Typical characteristic






5.3Typical characteristic






5.4Typical characteristic





6.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



7.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IPD50P03P4L-11	TO-252	2500	Tape and reel



8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.