

SOT-23 Bipolar Transistor 双极型三极管


■ Features 特点

PNP General Purpose 通用

HF

RoHS

Pb



■ Absolute Maximum Ratings 最大额定值

Characteristic 特性参数	Symbol 符号	BC807- 16/25/40 -6AF	BC808- 16/25/40 -6AF	Unit 单位
Collector-Base Voltage 集电极基极电压	V_{CBO}	-50	-30	V
Collector-Emitter Voltage 集电极发射极电压	V_{CEO}	-45	-25	V
Emitter-Base Voltage 发射极基极电压	V_{EBO}	-5	-5	V
Collector Current 集电极电流	I_C	-500	-800	mA
Power dissipation 耗散功率	$P_C(T_a=25^{\circ}C)$	300		mW
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	417		$^{\circ}C/W$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	-55to+150 $^{\circ}C$		

■ Device Marking 产品打标


H_{FE}		100-250(-16)	160-400(-25)	250-600(-40)
Mark	BC807-16/25/40-6AF	5A	5B	5C
	BC808-16/25/40-6AF	5E	5F	5G

■Electrical Characteristics 电特性


(TA=25℃ unless otherwise noted 如无特殊说明, 温度为 25℃)

Characteristic 特性参数		Symbol 符号	Min 最小值	Type 典型值	Max 最大值	Unit 单位
Collector-Base Breakdown Voltage 集电极基极击穿电压 (IC= -10μA, IE=0)	BC807-16/25/40-6AF BC808-16/25/40-6AF	BV _{CBO}	-50 -30	—	—	V
Collector-Emitter Breakdown Voltage 集电极发射极击穿电压 (IC= -10mA, IB=0)	BC807-16/25/40-6AF BC808-16/25/40-6AF	BV _{CEO}	-45 -25	—	—	V
Emitter-Base Breakdown Voltage 发射极基极击穿电压 (IE= -10μA, IC=0)		BV _{EBO}	-5	—	—	V
Collector-Base Leakage Current 集电极基极漏电流	BC807-16/25/40-6AF (V _{CB} =-50V,IE=0) BC808-16/25/40-6AF (V _{CB} =-30V,IE=0)	I _{CBO}	—	—	-100	nA
Emitter-Base Leakage Current 发射极基极漏电流 (V _{EB} = -4V, IC=0)		I _{EBO}	—	—	-100	nA
DC Current Gain 直流电流增益 (V _{CE} = -1V,IC= -100mA)	BC807/BC808-16-6AF BC807/BC808-25-6AF BC807/BC808-40-6AF	H _{FE}	100 160 250	—	250 400 600	
DC Current Gain 直流电流增益(V _{CE} = -1V,IC= -500mA)		H _{FE}	40			
Collector-Emitter Saturation Voltage 集电极发射极饱和压降(IC= -500mA, IB= -50mA)		V _{CE(sat)}	—	—	-0.7	V
Base-Emitter Saturation Voltage 基极发射极饱和压降(IC= -500mA, IB= -50mA)		V _{BE(sat)}	—	—	-1.2	V
Base-Emitter On Voltage 基极发射极导通电压(V _{CE} = -1V, IC= -300mA)		V _{BE(on)}	—	—	-1.2	V
Transition Frequency 特征频率(V _{CE} = -5V, IC= -10mA)		f _T	100	—	—	MHz
Output Capacitance 输出电容(V _{CB} = -10V, IE=0, f=1MHz)		C _{ob}	—	12	—	pF

■ Typical Characteristic Curve 典型特性曲线



■Dimension 外形封装尺寸



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.050	0.055
E1	2.250	2.550	0.089	0.100
e	0.900	1.00	0.035	0.039
e1	1.800	2.000	0.071	0.079
L	0.500	0.600	0.020	0.024
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°