

## 1.Description

Designed to protect voltage sensitive electronic components from ESD and other transients. Excellent clamping capability, low leakage, and fast response time provide best in class protection on designs that are exposed to ESD.

## 3.Applications


- Computers and peripherals
- PAD
- Audio and video equipment
- Cellular handsets and accessories
- Portable electronics

## 2.Features

- Bi-directional ESD protection of one line
- Low capacitance: 12pF(Typ.)
- Low reverse stand-off voltage: 5.0V
- Low reverse clamping voltage
- Low leakage current
- Excellent package:1.7mm×1.3mm×1.0mm

- Subscriber identity module(SIM) card protection
- Other electronics equipments communication systems

## 4.Pinning information



**SOD-323**



## 5. Absolute Maximum Ratings $T_A = 25^\circ\text{C}$

| Parameter                                              | Symbol              | Maximum    | Units            |
|--------------------------------------------------------|---------------------|------------|------------------|
| IEC 61000-4-2 ESD Voltage                              | $V_{\text{ESD}(1)}$ | $\pm 25$   | kV               |
| Air Model                                              |                     |            |                  |
| Contact Model                                          |                     | $\pm 25$   | kV               |
| JESD22-A114-B ESD Voltage                              |                     | $\pm 16$   | kV               |
| Per Human Body Model                                   |                     |            |                  |
| ESD Voltage                                            |                     | $\pm 0.4$  | kV               |
| Machine Model                                          |                     |            |                  |
| Peak Pulse Power                                       | $P_{\text{PP}(2)}$  | 50         | W                |
| Peak Pulse Current                                     | $I_{\text{PP}(2)}$  | 5          | A                |
| Lead Solder Temperature – Maximum (10 Second Duration) | $T_L$               | 260        | $^\circ\text{C}$ |
| Junction Temperature                                   | $T_J$               | 150        | $^\circ\text{C}$ |
| Storage Temperature Range                              | $T_{\text{STG}}$    | -55 to 150 | $^\circ\text{C}$ |


Notes:

(1) Device stressed with ten non-repetitive ESD pulses.

(2) Non-repetitive current pulse 8/20 $\mu\text{s}$  exponential decay waveform according to IEC61000-4-5.




6.ESD standards compliance




ESD pulse waveform according to IEC61000-4-2

| Contact Discharge |                 | Air Discharge |                 |
|-------------------|-----------------|---------------|-----------------|
| Level             | Test Voltage kV | Level         | Test Voltage kV |
| 1                 | 2               | 1             | 2               |
| 2                 | 4               | 2             | 4               |
| 3                 | 6               | 3             | 8               |
| 4                 | 8               | 4             | 15              |



8/20μs pulse waveform according to IEC 61000-4-5

| ESD Class | Human Body Discharge V |
|-----------|------------------------|
| 0         | 0 ~ 249                |
| 1A        | 250 ~ 499              |
| 1B        | 500 ~ 999              |
| 1C        | 1000 ~ 1999            |
| 2         | 2000 ~ 3999            |
| 3A        | 4000 ~ 7999            |
| 3B        | 8000 ~ 15999           |



V-I characteristics for a uni-directional TVS

| Symbol    | Parameter                           |
|-----------|-------------------------------------|
| $V_C$     | Clamping Voltage @ $I_{PP}$         |
| $I_{PP}$  | Peak Pulse Current                  |
| $V_{BR}$  | Breakdown Voltage @ $I_T$           |
| $I_T$     | Test Current                        |
| $I_R$     | Reverse Leakage Current @ $V_{RWM}$ |
| $V_{RWM}$ | Reverse Standoff Voltage            |



## 7. Electrical Characteristic ( $T_A=25^{\circ}\text{C}$ unless otherwise noted)

| Parameter                 | Symbol       | Conditions                        | Min | Typ | Max | Units         |
|---------------------------|--------------|-----------------------------------|-----|-----|-----|---------------|
| Reverse stand off voltage | $V_{RWM(1)}$ |                                   |     |     | 5   | V             |
| Reverse leakage current   | $I_R$        | $V_{RWM}=5\text{V}$               |     |     | 0.1 | $\mu\text{A}$ |
| Breakdown voltage         | $V_{(BR)}$   | $I_T=1\text{mA}$                  | 5.8 |     | 7.8 | V             |
| Clamping voltage          | $V_{C(2)}$   | $I_{PP}=5\text{A}$                |     |     | 10  | V             |
| Junction capacitance      | $C_J$        | $V_R=0\text{V}$ , $f=1\text{MHz}$ |     | 12  | 15  | pF            |


Notes:

(1). Other voltages available upon request.

(2). Non-repetitive current pulse 8/20 $\mu\text{s}$  exponential decay waveform according to IEC61000-4-5.




8. Typical characteristic





## 9.SOD-323 Package Outline Dimensions




### DIMENSIONS (mm are the original dimensions)

| Symbol | A    | $b_p$ | C    | D    | E    | $H_E$ | $A_1$ | P    |
|--------|------|-------|------|------|------|-------|-------|------|
| Min    | 0.90 | 0.25  | 0.10 | 1.60 | 1.15 | 2.30  | 0.01  | 0.20 |
| Max    | 1.20 | 0.40  | 0.15 | 1.80 | 1.35 | 2.80  | 0.10  | 0.50 |



10.Ordering information



ww: Batch Code

| Order Code       | Package | Base QTY | Delivery Mode |
|------------------|---------|----------|---------------|
| UMW CESDBLC5V0D3 | SOD-323 | 3000     | Tape and reel |



## **11.Disclaimer**

---

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.