

1.Description

- Advanced Process Technology
- Dynamic dv/dt Rating
- Fast Switching
- Fully Avalanche Rated
- Lead-Free


2.Features

- $V_{DS(V)}=55V$
- $I_D=56A$
- $R_{DS(ON)}<16m\Omega(V_{GS}=10V)$

3.Pinning information

Pin	Symbol	Description
1	G	GATE
3	S	SOURCE
2	D	DRAIN

TO-252(DPAK)
top view



4.Absolute Maximum Ratings

Parameter		Symbol	Rating	Units
Continuous Drain Current, $V_{GS}=10V$	$T_C=25^{\circ}C$	I_D	56 ⑥	A
Continuous Drain Current, $V_{GS}=10V$	$T_C=100^{\circ}C$		40 ⑥	A
Pulsed Drain Current ①		I_{DM}	220	A
Power Dissipation	$T_C=25^{\circ}C$	P_D	110	W
Linear Derating Factor			0.71	W/ $^{\circ}C$
Gate-to-Source Voltage		V_{GS}	± 20	V
Single Pulse Avalanche Energy ②		E_{AS}	130	mJ
Avalanche Current ①		I_{AR}	34	A
Repetitive Avalanche Energy ①		E_{AR}	11	mJ
Peak Diode Recovery dv/dt ③		dv/dt	5	V/ns
Operating Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 175	$^{\circ}C$
Soldering Temperature, for 10 seconds			300 (1.6mm from case)	$^{\circ}C$



5. Thermal resistance rating

Parameter	Symbol	Typ	Max	Units
Junction-to-Case	$R_{\theta JC}$		1.4	°C/W
Junction-to-Ambient (PCB Mount) *	$R_{\theta JA}$		50	°C/W
Junction-to-Ambient	$R_{\theta JA}$		110	°C/W



6. Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$I_D=250\mu\text{A}$, $V_{GS}=0\text{V}$	55			V
Breakdown Voltage Temp. Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	$I_D=1\text{mA}$, Reference to 25°C		0.052		$\text{V}/^\circ\text{C}$
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10\text{V}$, $I_D=34\text{A}$ ④		11.8	16	$\text{m}\Omega$
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=10\text{V}$, $I_D=250\mu\text{A}$	2		4	V
Forward Transconductance	g_{FS}	$V_{DS}=25\text{V}$, $I_D=34\text{A}$	30			S
Drain-to-Source Leakage Current	I_{DSS}	$V_{DS}=55\text{V}$, $V_{GS}=0\text{V}$			20	μA
		$V_{DS}=44\text{V}$, $V_{GS}=0\text{V}$, $T_J=150^\circ\text{C}$			250	μA
Gate-to-Source Forward Leakage	I_{GSS}	$V_{GS}=20\text{V}$			200	nA
Gate-to-Source Reverse Leakage		$V_{GS}=-20\text{V}$			-200	nA
Total Gate Charge	Q_g	$I_D=34\text{A}$		70	110	nC
Gate-to-Source Charge	Q_{gs}	$V_{DS}=44\text{V}$		16	23	nC
Gate-to-Drain ("Miller") Charge	Q_{gd}	$V_{GS}=10\text{V}$ ④		19	29	nC
Turn-On Delay Time	$t_{D(on)}$	$V_{DD}=28\text{V}$, $I_D=34\text{A}$ $R_G=6.8\Omega$, $V_{GS}=10\text{V}$ ④		15		ns
Rise Time	t_r			130		ns
Turn-Off Delay Time	$t_{D(off)}$			55		ns
Fall Time	t_f			78		ns
Internal Drain inductance	L_D	Between lead, 6mm (0.25in.) from package and center of die contact		4.5		nH
Internal Source inductance	L_S			7.5		nH
Input Capacitance	C_{iss}	$V_{GS}=0\text{V}$, $V_{DS}=25\text{V}$ $f=1\text{MHz}$, See Fig. 5 $V_{GS}=0\text{V}$, $V_{DS}=1\text{V}$, $f=1\text{MHz}$ $V_{GS}=0\text{V}$, $V_{DS}=44\text{V}$, $f=1\text{MHz}$ $V_{GS}=0\text{V}$, $V_{DS}=0\text{V}$ to 44V		2430		pF
Output Capacitance	C_{oss}			470		pF
Reverse Transfer Capacitance	C_{rss}			100		pF
Output Capacitance	C_{oss}			2040		pF
Output Capacitance	C_{oss}			350		pF
Effective Output Capacitance ⑤	$C_{oss \text{ eff.}}$			350		pF




Source-Drain Ratings and Characteristics						
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode.			56 ⑥	A
Pulsed Source Current (Body Diode) ①	I_{SM}				220	
Diode Forward Voltage	V_{SD}	$T_J=25^\circ\text{C}$, $I_S=34\text{A}$, $V_{GS}=0\text{V}$ ④			1.3	V
Reverse Recovery Time	t_{rr}	$T_J=25^\circ\text{C}$, $I_F=34\text{A}$ $di/dt=100\text{A}/\mu\text{s}$ ④		62	93	ns
Reverse Recovery Charge	Q_{rr}			170	260	nC
Forward Turn-On Time	t_{on}	Intrinsic turn-on time is negligible (turn-on is dominated by L_S+L_D)				

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting $T_J=25^\circ\text{C}$, $L=0.22\text{mH}$, $R_G=25\Omega$, $I_{AS}=34\text{A}$.
- ③ $ISD \leq 34\text{A}$, $di/dt \leq 190\text{A}/\mu\text{s}$, $V_{DD} \leq V_{(BR)DSS}$, $T_J \leq 175^\circ\text{C}$.
- ④ Pulse width $\leq 300\mu\text{s}$; duty cycle $\leq 2\%$.
- ⑤ C_{oss} eff. is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS} .
- ⑥ Calculated continuous current based on maximum allowable junction temperature. Package limitation current is 30A.




7.1 Typical Characteristics






7.2Typical Characteristics





7.3Typical Characteristics





7.4 Typical Characteristics




Figure 12a: Switching Time Test Circuit




Figure 12b: Switching Time Waveforms




Figure 13a: Unclamped Inductive Test Circuit




Figure 13b: Unclamped Inductive Waveforms




Figure 14a: Basic Gate Charge Waveform





Figure 14b: Gate Charge Test Circuit



8.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A1	A2	A3	b	c	D	D1	D2	E	E1	E2	e	L1	L2	L3	θ
Min	0.00	2.18	0.90	0.65	0.46	6.35	4.95	4.32	9.40	5.97	5.21	2.286 BSC	0.89	1.70	0.60	0.00
Max	0.13	2.39	1.10	0.85	0.61	6.73	5.46	4.90	10.41	6.22	5.38		1.27	1.90	1.00	8.00



9.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRFR2405TR	TO-252	2500	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.