

1. Description

The UMW MCP1415/6 device is a low voltage power MOSFET and IGBT in phase gate driver. Proprietary latch-immune of CMOS technology enables single-chip integrated architectures with high robustness. The UMW MCP1415/6 logic input level is compatible with CMOS or TTL logic output levels down to 3.3V. The output driver has internal Undervoltage Lockout (UVLO) circuitry with hysteresis and buffer stage of output current. The UMW MCP1415/6 is designed to operate over a wide VCC range of 5 V to 25 V and wide temperature range of -40°C to 125°C.

2. Applications



- Switch-Mode Power Supplies
- General Gate Driver
- Driving MOSFETs and IGBTs

3. Features

- Input output in phase / out of phase
- Compatible with 3.3V、5V input logic
- 4.5 to 25-V Single-Supply Range
- High capacitance load driving capability
- Operating Temperature Range of -40 to 125°C
- Undervoltage Lockout
- Turn on/Turn off Delays:
 - Ton/Toff =25ns/25ns
- 2-A Peak Source and Sink-Drive Current
- SOT23-5 Package




4. Pin Configuration





5.1 Pinning Information




UMW MCP1415 pin description

| Number | Symbol | Description |
|--------|------------------|----------------------------------|
| 1 | NC | No connection |
| 2 | V_{DD} | Power supply |
| 3 | IN | Logic input |
| 4 | GND | Ground |
| 5 | \overline{OUT} | Gate driven output(out-of-phase) |



5.2 Pinning Information



UMW MCP1416 pin description

| Number | Symbol | Description |
|--------|----------|------------------------------|
| 1 | NC | No connection |
| 2 | V_{DD} | Power supply |
| 3 | IN | Logic input |
| 4 | GND | Ground |
| 5 | OUT | Gate driven output(in-phase) |



6. Absolute Maximum Ratings

Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. All voltages are with respect to COM unless otherwise noted, Currents are positive into, negative out of the specified terminal, environment temperature is 25°C.

| Parameter | Symbol | Min | Max | Units |
|----------------------|----------|------|--------------|-------|
| Supply voltage range | V_{CC} | -0.3 | 25 | V |
| OUT voltage range | V_O | -0.3 | $V_{CC}+0.3$ | V |
| IN voltage | V_{IN} | -12 | $V_{CC}+0.3$ | V |

7. Thermal Information

| Parameter | Symbol | Min | Max | Units |
|--------------------------------|---------------|-----|-----|-------|
| Thermal Resistance | $R_{th_{JA}}$ | | 151 | °C/W |
| Storage Temperature | T_S | -55 | 150 | °C |
| Operating Junction Temperature | T_J | | 150 | °C |
| Lead Temperature | T_L | | 300 | °C |

8. Recommended Operating Conditions

To properly operate, device should be used in the following recommended conditions. All voltages are with respect to COM unless otherwise noted, Currents are positive into, negative out of the specified terminal, environment temperature is 25°C.

| Parameter | Symbol | Min | Max | Units |
|----------------------|----------|-----|----------|-------|
| Supply voltage range | V_{CC} | 4.5 | 20 | V |
| OUT voltage range | V_O | 0 | V_{CC} | V |
| IN voltage | V_{IN} | -10 | V_{CC} | V |
| Ambient temperature | T_A | -40 | 125 | °C |



9. Electrical Characteristics

$T_A=25^\circ\text{C}$, $V_{CC}=15\text{V}$ (unless otherwise noted)

| Parameter | Symbol | Min | Typ | Max | Units |
|--|------------------------------------|---------------|-----|------|---------------|
| Input signal high threshold | V_{IH} | 2.5 | | | V |
| Input signal low threshold | V_{IL} | | | 0.8 | V |
| Under voltage Lockout (UVLO) turn-on threshold V_{CC} | V_{CCUV+} | | 4 | | V |
| Under voltage Lockout (UVLO) turn-off threshold V_{CC} | V_{CCUV-} | | 3.9 | | V |
| UVLO threshold hysteresis V_{CC} | V_{CCUVHY} | | 0.1 | | V |
| Input current($IN=HIGH$) | $UMW\text{ MCP1416, IN}=5\text{V}$ | I_{IN+} | 50 | 100 | μA |
| | $UMW\text{ MCP1415, IN}=0\text{V}$ | | 150 | 300 | μA |
| Input current($IN=LOW$) | $UMW\text{ MCP1416, IN}=0\text{V}$ | I_{IN-} | | 5 | μA |
| | $UMW\text{ MCP1415, IN}=5\text{V}$ | | 100 | 200 | μA |
| High output voltage | V_{OH} | $V_{CC}-0.35$ | | | V |
| Low output voltage | V_{OL} | | | 0.35 | V |
| V_{CC} quiescent supply current | I_Q | | | 500 | μA |
| Output high short-circuit pulse current | I_{O+} | | 2 | | A |
| Output low short-circuit pulse current | I_{O-} | | 2 | | A |
| Rise time ($CL=1\text{nF}$) | t_R | | | 30 | ns |
| Fall time ($CL=1\text{nF}$) | t_F | | | 30 | ns |
| Turn-on propagation delay ($CL=1\text{nF}$) | t_{ON} | | 25 | 50 | ns |
| Turn-off propagation delay ($CL=1\text{nF}$) | t_{OFF} | | 25 | 50 | ns |



10. Function Description




Figure 1. UMW MCP1415 Input-Output waveform




Figure 2. UMW MCP1416 Input-Output waveform




Figure 3. UMW MCP1415 Propagation Time Waveform Definition




Figure 4. UMW MCP1416 Propagation Time Waveform Definition

11. Function Block Diagram




Figure 5. Function Block Diagram of UMW MCP1415




Figure 6. Function Block Diagram of UMW MCP1416

12. Application Message





Figure 7. Typical application circuit of UMW MCP1415/6

13. SOT23-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A | A1 | A2 | b | c | D | E1 | E | e | e1 | L | θ |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|----|
| Min | 1.050 | 0.000 | 1.050 | 0.300 | 0.100 | 2.820 | 1.500 | 2.650 | 0.950 | 1.800 | 0.300 | 0° |
| Max | 1.250 | 0.100 | 1.150 | 0.500 | 0.200 | 3.020 | 1.700 | 2.950 | BSC | 2.000 | 0.600 | 8° |



14. Ordering information



| Order Code | Marking | Package | Base QTY | Delivery Mode |
|-------------------|---------|---------|----------|---------------|
| UMW MCP1415T-E/OT | FYBU | SOT23-5 | 3000 | Tape and reel |
| UMW MCP1416T-E/OT | FZQM | SOT23-5 | 3000 | Tape and reel |



15.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.