

MESSRS.**SPECIFICATION FOR APPROVAL****承 認 书**

Product	PIEZO BUZZER ELEMENT
Part No.	HE-2739E-C (RoHS)
Customer	
Customer Part No.	

Approved By	Checked By	Made By
王台平 SEP-13-2023	曹丽萍 SEP-13-2023	LILY SEP-13-2023

常 州 华 龙 电 子 有 限 公 司
DRAGONSTATE ELECTRONIC CORPORATION

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081


1. Scope

This specification applies PIEZO ELEMENT HE-2739E-C (RoHS)

2. Characteristics

ITEM		CONDITION	
01	Type.	EXTERNAL -drive type sound element	
02	Resonant Frequency (KHz)	3.9± 0.5 at 25± 2°C, 45~60% RH	
03	Resonant Impedance (OHM)	300 OHM Max. at 25± 2°C, 45~60% RH	
04	Capacity (PF)	30000±30% at 120Hz	
05	Input Voltage	30Vp-p Max	
06	Plate Material	Stainless steel	
07	DC Resistance (MΩ) DC	10 Min	FLUKE 45 RATE:FAST MEASUREMENT TIME:1Sec(onlyfor* 20mm must be test)
08	Operating Temperature (°C)	-20 to +70	
09	Storage Temperature (°C)	-30 to +80	

3.Dimension



Connector: JST-SHR-02V 兼容品
 Wire: UL1571 AWG30

