

1.Description

The UMW MOC305x series devices are optocouplers composed of a GaAs infra-red light emitting diode and a singlecrystal silicon chip random phase photoelectric bidirectional thyristor.


2.Features

- Peak breakdown voltage 600V
- High isolation voltage between input and output($V_{ISO}=5000$ Vrms)
- Compact DIP (Dual In-line Package) housing
- Lead-free, RoHS compliant
- UL approved: UL1577, file No.E547318

3.Application

- Solenoid valve control
- Ballast
- Static AC power switch
- Incandescent lamp dimmer
- Microprocessor 115-240VAC peripheral interface
- Temperature control
- Motor control

4.Pinning information





5. Absolute Maximum Ratings

Parameter		Symbol	Value	Unit
Input				
Forward Current		I _F	60	mA
Backward Voltage		V _R	6	V
Power Dissipation		P _D	100	mW
Power dissipation Derating factor (above Ta=85°C)			3.8	mW/°C
Output				
Off-state output terminal voltage	UMW MOC305x	V _{DRM}	600	V
Peak repetitive surge current (pw=100μs,120pps)		I _{TSM}	1	A
On-state current (root mean square value)		I _{T(RMS)}	100	mA
Power Dissipation		P _C	300	mW
Power dissipation Derating factor (above Ta=85°C)			7.4	mW/°C
Total Power Dissipation		P _{TOT}	330	mW
Isolation Voltage		V _{ISO}	5000	Vrms
Operating Temperature		T _{OPR}	-55 to 110	°C
Storage Temperature		T _{STG}	-55 to 125	°C
Soldering Temperature (10s)		T _{SOL}	260	°C

Notes:

Conduct AC test at 40% ~60% relative humidity. At this time, pins 1, 2 and 3 are short-circuited, and pins 4, 5 and 6 are short-circuited.



6.Electro-optical Characteristics(T_A=25°C)

Parameter		Symbol	Conditions	Min	Typ	Max	Units
Input							
Forward Voltage		V _F	I _F =20mA		1.18	1.5	V
Back current		I _R	V _R =6V			10	μA
Output							
Off-state peak current		I _{DRM}	V _{DRM} =Rated V _{DRM} , I _F =0mA			100	nA
On-state peak voltage		V _{TM}	I _{TM} =100mA peak, I _F =Rated I _{FT}			2.5	V
Critical rise rate of off-state voltage		dv/dt	V _{PEAK} =400V, I _F =0	1000			V/μs
Transfer Characteristics							
LED trigger current	UMW MOC3051	I _{FT}	Main terminal Voltage =3V			15	mA
	UMW MOC3052					10	mA
	UMW MOC3053					5	mA
Maintain current		I _H			250		μA




7. Typical Characteristic

Figure 1: LED Forward Voltage vs. Forward Current	Figure 2: On-State Characteristics
Figure 3: Trigger Current vs. Ambient Temperature	Figure 4: LED Current Required to Trigger vs. LED Pulse Width
Figure 5: dv/dt vs. Temperature	Figure 6: Leakage Current, I _{DRM} vs. Temperature



8.Static dv/dt test circuit and waveform



The high voltage pulse applied to the output end of the device under test through the RC circuit is set to the desired V_{PEAK} value. LED current does not need to be added. Waveform V_T is monitored with X100 probe. By adjusting the R_{TEST} value, dv/dt (slope) increases until the device under test is observed to be triggered (waveform collapse). Dv/dt then drops until the device under test stops being triggered. At this time, dv/dt can be calculated by recording the value of τRC .


$$dv/dt = \frac{0.632 \times V_{PEAK}}{\tau RC}$$

For example, the voltage peak of UMW MOC305x series $V_{PEAK}=600V$. Then the dv/dt value can be calculated as follows:

$$dv/dt = \frac{0.632 \times 600}{\tau RC} = \frac{379}{\tau RC}$$



9.DIP-6/SOP-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	B	B1	B2	b	c	D	D1	E
Min	6.45	7.45	0.2	8.7	7.07	1.625	1.595	3.45	4.2	7.45	6.45	0.76
Max	6.55	7.75	(typ.)	9.1	7.14	(typ.)	1.655	3.55	4.4	7.75	6.55	(typ.)

Symbol	E1	F
Min	10.0	3.45
Max	10.4	3.55



10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW MOC3051M	MOC3051	DIP-6	3250	Tape and reel
UMW MOC3052M	MOC3052	DIP-6	3250	Tape and reel
UMW MOC3052SM	MOC3052	SOP-6	1000	Tape and reel
UMW MOC3053M	MOC3053	DIP-6	3250	Tape and reel
UMW MOC3053SM	MOC3053	SOP-6	1000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.