


1.Features

- High DC current gain
- Complementary to KTA1298
- 2SC3265 TRANSISTOR (NPN)

2.Pinning Information

Pin	Symbol	Description
1	B	BASE
2	E	EMITTER
3	C	COLLECTOR

SOT-23



3.Absolute Maximum Ratings $T_A = 25^{\circ}\text{C}$

Parameter	Symbol	Value	Units
Collector-Base Voltage	V_{CBO}	35	V
Collector-Emitter Voltage	V_{CEO}	30	V
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current -Continuous	I_C	800	mA
Collector Power Dissipation	P_C	200	mW
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Storage Temperature	T_{STG}	-55 to 150	$^{\circ}\text{C}$



4. Electrical Characteristics $T_A = 25^\circ\text{C}$


Parameter	Symbol	Conditions	Min	Typ	Max	Units
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = 100\mu\text{A}$, $I_E = 0$	35			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = 10\text{mA}$, $I_B = 0$	30			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = 100\mu\text{A}$, $I_C = 0$	5			V
Collector cut-off current	I_{CBO}	$V_{CB} = 30\text{V}$, $I_E = 0$			0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB} = 5\text{V}$, $I_C = 0$			0.1	μA
DC current gain	h_{FE}	$V_{CE} = 1\text{V}$, $I_C = 100\text{mA}$	100		320	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = 500\text{mA}$, $I_B = 20\text{mA}$			0.5	V
base-emitter voltage	V_{BE}	$V_{CE} = 1\text{V}$, $I_C = 10\text{mA}$	0.5		0.8	V
Transition frequency	f_T	$V_{CB} = 5\text{V}$, $I_C = 10\text{mA}$, $f = 100\text{MHz}$		120		MHz
Collector output capacitance	C_{ob}	$V_{CB} = 10\text{V}$, $I_E = 0$, $f = 1\text{MHz}$		13		pf

5. Classification of h_{FE}

Rank	O	Y
Range	100-200	160-320
Marking	EO	EY




6. Typical Characteristics





7.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b_p	C	D	E	H_E	A1	L_p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



8.Ordering information



Order Code	Package	Base QTY	Delivery Mode
UMW 2SC3265	SOT-23	3000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.