

1.Description

The UMW SN74LVC1G00 is a 2-input NAND integrated circuit, which can realize the mathematical logic operation of $Y = \overline{A \times B}$ and $Y = \overline{A} + \overline{B}$. Advanced CMOS process design is adopted, which has the working characteristics of low power consumption and high output driving capability. The chip can work normally when the power supply voltage V_{CC} is between 1.65V and 5.5V V. And UMW SN74LVC1G00 has a variety of small package shapes, It can be widely used in high-end precision instruments, miniaturized low-power handheld devices, artificial intelligence and other fields.


2.Features

- Low input current: 0.1 μ A typical
- Low static power consumption: 0.1 μ A typical
- High output drive: $V_{CC}=4.5V$, more than 32MA
- Wide working voltage range: 1.65V to 5.5V
- Package form: SOT23-5/SC70-5/SOT-553, SFN/SON-6, DSBGA-5, X2SON-5

3.Product Usage

- Portable audio interface
- digital television
- Wireless headphones, smart watches, etc.
- Blu-ray player and home theater
- Solid state drive
- Smart wearable devices

4.Pinning information





5.Pin Function

Pin				Description
Name	SOT23-5/SC70-5/SOT-553, DSBGA-5	DFN/SON-6	X2SON-5	
A	1	1	2	Input
B	2	2	1	Input
GND	3	3	3	Ground
Y	4	4	4	Output
V _{CC}	5	6	5	Power pin
NC		5		Not connected

Notes: NC null pin, no connecting wire inside.

6.Limit parameter


Parameter	Symbol	Limit Value	Unit
operating voltage	V _{CC}	6.5	V
input	V _{IN}	-0.5 ~ 6.5	V
Output voltage(1)	V _{OUT}	-0.5 ~ 6.5	V
Single pin output current	I _{OUT}	25	mA
or V _{CC} current.	I _{CC}	50	mA
Storage temperature	T _S	-65 to 150	°C
Pin welding temperature	T _W	260, 10s	°C
Working temperature	T _A	-40 to 105	°C

Note:

1. In the power-off state of V_{CC}=0V, the limit voltage that the output can bear,
2. Limit parameter refers to the limit value that can't be exceeded under any conditions. If it exceeds this limit value, it may cause physical damage such as product deterioration; At the same time, the chip can't work normally when it is close to the limit parameters.



7.Principle Logic Diagram



Function Table

Input		Output
A	B	Y
L	L	H
L	H	H
H	L	H
H	H	L



8. Electrical Characteristics


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Operating Voltage	V_C		1.65		5.5	V
Input High Level Voltage	V_{IH}	$V_C=1.65V\sim1.95V$	$0.65*V_C$			V
		$V_C=2.3V\sim2.7V$	1.7			V
		$V_C=3V\sim5.5V$	$0.7*V_C$			V
Low-level Input Voltage	V_{IL}	$V_C=1.65V\sim1.95V$			$0.35*V_C$	V
		$V_C=2.3V\sim2.7V$			0.7	V
		$V_C=3V\sim5.5V$			$0.3*V_C$	V
Input Voltage	V_I		0		5.5	V
Output Voltage	V_O		0		V_C	V
High Level Output Current	I_{OH}	$V_C=1.65V$			-4	mA
		$V_C=2.3V$			-8	mA
		$V_C=3V$			-16	mA
		$V_C=4.5V$			-32	mA
Low Level Output Current	I_{OL}	$V_C=1.65V$			4	mA
		$V_C=2.3V$			8	mA
		$V_C=3V$			16	mA
		$V_C=4.5V$			32	mA
High Level Load Voltage	V_{OH}	$I_{OH}=-100\mu A, V_{CC}=1.6 \text{ to } 5.5V$	$V_{CC}-0.1$		5.5	V
		$I_{OH}=-4mA, V_{CC}=1.65V$	1.2			V
		$I_{OH}=-8mA, V_{CC}=2.3V$	1.9			V
		$I_{OH}=-16mA, V_{CC}=3V$	2.4			V
		$I_{OH}=-32mA, V_{CC}=4.5V$	3.8			V
Low Level Load Voltage	V_{OL}	$I_{OH}=100\mu A, V_{CC}=1.6 \text{ to } 5.5V$			0.1	V
		$I_{OH}=4mA, V_{CC}=1.65V$			0.45	V
		$I_{OH}=8mA, V_{CC}=2.3V$			0.3	V
		$I_{OH}=16mA, V_{CC}=3V$			0.4	V
		$I_{OH}=32mA, V_{CC}=4.5V$			0.55	V



Parameter	Symbol		Conditions	Min.	Typ.	Max.	Unit
Incoming Current	I _I	A	V _I =5.5V or GND	0~5.5V	0.1	±5	μA
		B			0.1	±5	μA
Turn-off Current	I _{OFF}	V _I	V _I =5.5V	0	0.1	±10	μA
		V _O	V _O =5.5V	0	0.1	±10	μA
Operational Current	I _{CC}		V _I =5.5V, I _O =0	1.65V~5.5V	0.1	10	μA
			V _I =GND, I _O =0		0.1	10	μA
Working Current Variation Value	ΔI _{CC}		A=V _{CC} -0.6V B=V _{CC} or GND	3V~5.5V	25		μA
			B=V _{CC} -0.6V A=V _{CC} or GND		25		μA

$T_a=25^{\circ}C$ $V(298)=5.0V$, $t_r \leq 20ns$. See test method.

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Maximum transmission delay time a, B to Y		C=15pF		10		ns
				10		ns




Note: 1. CL capacitor is external chip capacitor (0603), which is connected close to the output pin, and the capacitor ground is close to the chip GND;

2. Input: port input level, $f=500\text{kHz}$, $D=50\%$; $t_r=t_f \leq 20\text{ns}$;

3. Output: Y-terminal output test.



9.1 SOT23-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E1	E	e	e1	L	θ
Min	1.050	0.000	1.050	0.300	0.100	2.820	1.500	2.650	0.950	1.800	0.300	0°
Max	1.250	0.100	1.150	0.500	0.200	3.020	1.700	2.950	BSC	2.000	0.600	8°



9.2 SC70-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	θ
Min	0.90	0.00	0.90	0.15	0.08	2.05	1.15	2.15	0.65	1.20	0.26	7°
Max	1.10	0.10	1.00	0.35	0.15	2.25	1.35	2.45	TYP	1.40	0.46	REF.



9.3 SON-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1
Min	0.95	0.95	-	0.7	0.35	0.1	0.35	0.12	0.11	0.00
Max	1.05	1.05	0.4				0.45	0.22	TYP	0.05



9.4 DFN(1*1.5) Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	H
Min	0.95	1.4	1	0.5	0.6	0.05	0.3	0.25	0.15	-	0.00	0.127
Max	1.05	1.5				TYP	0.4	0.35	0.25	0.6	0.05	TYP



9.5 DSBGA-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	C
Min	0.5	-	0.05
Max	TYP	0.05	-



9.6 X2SON-5 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1	L	L1
Min	0.75	-	0.05	0.48	0.17	0.06	0.25	0.23	0.15	0.26	0.17	0.1
Max	0.85	0.4			0.27			0.32	0.35		0.27	

Symbol	H
Min	0.00
Max	0.05



9.7 SOT-553 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	c	D	E	E1	e	e1
Min	1.50	1.10	0.13	1.50	0.50	0.15	0.20	0.50	0.00	0.08
Max	1.70	1.30	0.27	1.70		0.25	0.40	0.60	0.05	0.18



10.Ordering information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SN74LVC1G00DBVR	C00K	SOT23-5	3000	Tape and reel
UMW SN74LVC1G00DCKR	CA5	SC70-5	3000	Tape and reel
UMW SN74LVC1G00DSFR	CA	SON-6	5000	Tape and reel
UMW SN74LVC1G00DRYR	CA	DFN(1*1.5)	5000	Tape and reel
UMW SN74LVC1G00YZPR	CA7	DSBGA-5	3000	Tape and reel
UMW SN74LVC1G00DPWR	H4	X2SON-5	3000	Tape and reel
UMW SN74LVC1G00DRLR	CA7	SOT-553	4000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.