


SOT-89-3L Bipolar Transistor 双极型三极管

■ Features 特点

NPN High Voltage 高压

■ Absolute Maximum Ratings 最大额定值



Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Collector-Base Voltage 集电极基极电压	V_{CBO}	160	V
Collector-Emitter Voltage 集电极发射极电压	V_{CEO}	160	V
Emitter-Base Voltage 发射极基极电压	V_{EBO}	6	V
Collector Current 集电极电流	I_C	1000	mA
Power dissipation 耗散功率	$P_C(T_a=25^{\circ}C)$	500	mW
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	250	$^{\circ}C/W$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	-55to+150 $^{\circ}C$	

■ Device Marking 产品打标







$H_{FE}(1)$	60-120(R)	100-200(O)	160-320(Y)
Mark	2383R	2383O	2383Y

■Electrical Characteristics 电特性


(TA=25℃ unless otherwise noted 如无特殊说明, 温度为 25℃)

Characteristic 特性参数	Symbol 符号	Min 最小值	Type 典型值	Max 最大值	Unit 单位
Collector-Base Breakdown Voltage 集电极基极击穿电压(IC=100uA, IE=0)	BV _{CBO}	160	—	—	V
Collector-Emitter Breakdown Voltage 集电极发射极击穿电压(IC=1mA, IB=0)	BV _{CEO}	160	—	—	V
Emitter-Base Breakdown Voltage 发射极基极击穿电压(IE=10uA, IC=0)	BV _{EBO}	6	—	—	V
Collector-Base Leakage Current 集电极基极漏电流(V _{CB} =150V, IE=0)	I _{CBO}	—	—	1	μA
Collector-Emitter Leakage Current 集电极发射极漏电流(V _{CE} =150V, R _{EB} =10MΩ)	I _{CER}	—	—	10	μA
Emitter-Base Leakage Current 发射极基极漏电流(V _{EB} =6V, IC=0)	I _{EBO}	—	—	1	μA
DC Current Gain 直流电流增益(V _{CE} =5V, IC=200mA)	H _{FE} (1)	60	—	320	
DC Current Gain 直流电流增益(V _{CE} =5V, IC=10mA)	H _{FE} (2)	40	—	—	
Collector-Emitter Saturation Voltage 集电极发射极饱和压降(IC=500mA, IB=50mA)	V _{CE(sat)}	—	—	1	V
Base-Emitter Saturation Voltage 基极发射极饱和压降(V _{CE} =5V, IC=5mA)	V _{BE}	—	—	0.75	V
Transition Frequency 特征频率(V _{CE} =5V, IC=200mA)	f _T	20	—	—	MHz
Output Capacitance 输出电容(V _{CB} = 5V, IE=0, f=1MHz)	C _{ob}	—	12	—	pF

■ Typical Characteristic Curve 典型特性曲线



■Dimension 外形封装尺寸



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.40	1.60	0.055	0.063
B	0.40	0.56	0.016	0.022
B1	0.35	0.48	0.014	0.019
C	0.35	0.44	0.014	0.017
D	4.40	4.60	0.173	0.181
D1	1.35	1.83	0.053	0.072
e	1.45	1.55	0.057	0.061
e1	2.95	3.05	0.116	0.120
E	2.29	2.60	0.090	0.102
H	3.75	4.25	0.148	0.167
L	0.80	1.20	0.031	0.047