



1. Description

The UMW LM324 consists of four independent, high gain, internally frequency compensated operational amplifiers which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage. Application areas include transducer amplifiers, DC gain blocks and all the conventional op amp circuits.

2. Features

- Wide range of supply voltages
- Low supply current drain independent of supply voltage
- Low input biasing current
- Low input offset voltage and offset current
- Input common-mode voltage range includes ground
- Differential input voltage range equal to the power supply voltage
- DC voltage gain 100 V/ mV Typ
- Internally frequency compensation

3. Pinning information





4.Absolute Maximum Ratings

Parameter	Symbol	Value	Units
Supply voltage	V_{CC}	± 16 or 32	V
Input voltage, LM324	V_i	-0.3 to 32	V
Differential input voltage	V_{id}	32	V
Power dissipation: D suffix	P_{tot}	400	mW
Output short-circuit duration		Infinite	
Operating temperature range, LM324	T_{OPER}	0 to 70	$^{\circ}C$



5. Electrical Characteristics

Parameter	Symbol	Conditions		Min	Typ	Max	Units
Input offset voltage	V_{IO}	$V_{CC}=5V$ to MAX	25°C		3	7	mV
		$V_{IC}=V_{ICR}$ min, $V_O=1.4V$	Full temperature range			9	mV
Average temperature coefficient of input offset voltage	αV_{IO}		Full temperature range		7		$\mu V/^{\circ}C$
Input offset current	I_{IO}	$V_O=1.4V$	25°C		2	50	nA
			Full temperature range			150	nA
Average temperature coefficient of input offset current	αI_{IO}		Full temperature range		10		$pA/^{\circ}C$
Input bias current	I_{IB}	$V_O=1.4V$	25°C		-20	-200	nA
			Full temperature range			-400	nA
Common-mode input voltage range	V_{ICR}	$V_{CC}=5V$ to MAX	25°C			$V_{CC}-1.5$	V
			Full temperature range			$V_{CC}-2.0$	V
High-level output voltage	V_{OH}	$R_L=2k\Omega$	25°C	$V_{CC}-1.5$			V
		$V_{CC}=MAX$	Full temperature range	26			
		$R_L=2k\Omega$	Full temperature range				
		$V_{CC}=MAX$ $R_L=10k\Omega$	Full temperature range	27	28		
Low-level output voltage	V_{OL}	$R_L=10k\Omega$	Full temperature range		5	20	mV
Large-signal differential voltage amplification	A_{VD}	$V_{CC}=15V$ $V_O=1V$ to 11V $R_L \geq 2k\Omega$	25°C	25	100		V/mV
			Full temperature range	15			



Parameter	Symbol	Conditions		Min	Typ	Max	Units
Common-mode rejection ratio	CMRR	$V_{CC}=5V$ to MAX $V_{IC}=V_{ICR}$ min	25°C	65	80		dB
Supply voltage rejection ratio ($\Delta V_{CC}/\Delta V_{IO}$)	k_{SVR}	$V_{CC}=5V$ to MAX	25°C	65	100		dB
Crosstalk attenuation	V_{O1}/V_{O2}	$f=1kHz$ to 20 kHz	25°C		120		dB
Output current	I_O	$V_{CC}=15V$ $V_{ID}=1V, V_O=0$	25°C	-20	-30		mA
			Full temperature range	-10			
		$V_{CC}=15V$ $V_{ID}=-1V, V_O=15V$	25°C	10	20		mA
			Full temperature range	5			
		$V_{ID}=-1V$ $V_O=200mV$	25°C	12	30		μA
Short-circuit output current	I_{OS}	V_{CC} at 5 V, GND at -5V, $V_O=0$	25°C		± 40	± 60	mA
Supply current (four amplifiers)	I_{CC}	$V_O=2.5V$, No load	Full temperature range		0.7	1.2	mA
		$V_{CC}=MAX$ $V_O=0.5V_{CC}$, No load	Full temperature range		1.5	3	mA

* All characteristics are measured under open loop conditions with zero common-mode input voltage unless otherwise specified.

"MAX" V_{CC} for testing purposes is 30 V. Operating temperature 0 - 70° C.



6. Typical Characteristic




Figure 1: Output Current Characteristic




Figure 2: Output Pull Current Characteristic




Figure 3: Pull Current Limit




Figure 4: Voltage Follower Large Signal Pulse Response (50pF)




Figure 5: Common Mode Rejection Ratio





Figure 6: The relationship between the maximum output swing and frequency ($V_{CC} = 15V$)



7.1 SOP-14 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	C	D	E	E1	e	h	L
Min	-	0.05	1.35	0.65	0.203	0.17	8.45	5.80	3.80	1.24	0.25	0.40
Max	1.75	0.25	1.55	0.75	0.305	0.25	8.85	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°



7.2 TSSOP-14 Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	b1	c	c1	D	E	E1	e	L1
Min	-	0.05	0.90	0.20	0.19	0.13	0.120	4.90	6.20	4.30	0.65	0.85
Max	1.20	0.15	1.05	0.28	0.25	0.17	0.14	5.10	6.60	4.50	BSC	1.15

Symbol	L	θ
Min	0.45	0°
Max	0.75	8°



8.Ordering information

SOP-14

UMW yyww
LM324A

TSSOP-14

LM324
UMW yww


yy: Year Code

ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW LM324ADR	LM324A	SOP-14	2500	Tape and reel
UMW LM324PT	LM324	TSSOP-14	4000	Tape and reel
UMW LM324PWR	LM324	TSSOP-14	4000	Tape and reel
UMW LM324APT	LM324	TSSOP-14	4000	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.