



1.Description

NPNN five-layer structure of silicon bidirectional devices; with independent intellectual property rights of single-sided digging technology, table glass passivation process; multi-layer metallized electrodes on the back; with high blocking voltage and high temperature stability.

2.Features

vacuum cleaners, power tools and other motor speed controllers; solid state relays; heating controllers (temperature regulation); other phase control circuits.

3.Pinning Information



TO-220A



4. Absolute maximum ratings ($T_J=25^{\circ}\text{C}$ unless otherwise stated)

Parameter			Symbol	Values	Units
RMS on-statecurrent(full sine wave)	BTA	T _C =80°C	I _{T(RMS)}	16	A
Non repetitive surge peakon-state current (full cycle,T _J initial=25°C)	F=50HZ, tp=20ms		I _{TSM}	160	A
I ² t value for fusing	tp=10ms		I ² t	144	A²S
Critical rate of rise of on-state current I _G =2 x I _{GT} , tr≤100ns	T _J =125		di/dt	50	A/us
Off state repetitive peak voltage Reverse repetitive peak voltage	T _J =25°C		V _{DRM} /V _{RRM}	600/800	V
Peak gate current	tp=20us	T _J =150°C	I _{GM}	4	A
Average gate power dissipation		T _J =150°C	P _{G(AV)}	1	W
Storage junction temperature range			T _{STG}	-40 to 150	°C
Operating junction temperature range			T _J	-40 to 150	°C



5.1 Electrical characteristics (3 quadrants)

Parameter	Quadrant	Range	Symbol	Values			Units
$V_D=12V$ $R_L=100\Omega$	I	MAX	I_{GT}	Min	Typ	Max	mA
		MAX		15	25	35	mA
$V_D=V_{DRM}$, $R_L=3.3k\Omega$, $T_J=125^\circ C$	II	MAX	V_{GT}	1.5			V
	III	MIN	V_{GD}	0.2			V
$I_T=100mA$		MAX	I_H	60			mA
$I_G=1.2 \times I_{GT}$		MAX	I_L	I - III		60	mA
		MAX		II		100	mA
$V_D = 67\% V_{DRM}$, gate open, mA, $T_J=125^\circ C$		MIN	dv/dt	500			V/us
Critical rise rate of commutation voltage $T_J=150^\circ C$		MIN	(dv/dt)c	10			V/us

5.2 Electrical characteristics (4 quadrants)

Parameter	Quadrant	Range	Symbol	value				Units
$V_D=12V$ $R_L=100\Omega$	I - II - III	MAX	I_{GT}	I	II	III	IV	mA
		MAX		≤ 25	≤ 35	≤ 35	≤ 120	mA
$V_D=V_{DRM}$, $R_L=3.3k\Omega$, $T_J=125^\circ C$	IV	MAX	V_{GT}	1.5				V
		MIN	V_{GD}	0.2				V
$I_T=500mA$		MAX	I_H	60				mA
$I_G=1.2 \times I_{GT}$		MAX	I_L	60				mA
		MAX		100				mA
$V_D = 67\% V_{DRM}$, gate open, mA, $T_J=125^\circ C$		MIN	dv/dt	500				V/us
Critical rise rate of commutation voltage $T_J=150^\circ C$		MIN	(dv/dt)c	10				V/us



6.Static Parameters

Parameter			Symbol	Values	Units
$I_{TM}=32A$	$T_J=25^{\circ}C$	MAX	V_{TM}	1.5	V
threshold on-state voltage	$T_J=150^{\circ}C$	MAX	V_{T0}	0.87	V
Dynamic resistance	$T_J=150^{\circ}C$	MAX	R_d	14.6	mΩ
$V_{DRM}=V_{RRM}$	$T_J=25^{\circ}C$	MAX	I_{DRM}, I_{RRM}	5	uA
	$T_J=125^{\circ}C$	MAX		1	mA
Junction to ambient	BTA	MAX	$R_{th(j-c)}$	2.1	°C/W



7. Typical Characteristic




Figure 1: Maximum power dissipation versus RMS on-state current




Figure 2: RMS on-state current versus case temperature




Figure 3: Surge peak on-state current versus number of cycles




Figure 4: On-state characteristics (maximum values)




Figure 5: Sinusoidal pulse with width $t_p < 20\text{ms}$ value of I^2t ($dIdt < 50\text{A}\mu\text{s}$)





Figure 6: Holding current and latching current versus junction temperature



8.TO-220A Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	C	C1	C2	C3	Φ	F	F1	F2	F3	G1	G2
Min	10.000	28.700	6.400	9.040	13.160	3.700	4.350	1.220	3.130	2.300	1.220	0.750
Max	10.200	29.100	6.500	9.240	13.460	3.800	4.650	1.320	3.330	2.700	1.320	0.850

Symbol	M	K
Min	0.450	2.540
Max	0.550	



9.Ordering information

BTA16-600BW
UMW yyww

yy: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW BTA16-600BRG	BTA16-600B	TO-220A	1000	Tube and box
UMW BTA16-600CRG	BTA16-600C	TO-220A	1000	Tube and box
UMW BTA16-800BRG	BTA16-800B	TO-220A	1000	Tube and box
UMW BTA16-600BWRG	BTA16-600BW	TO-220A	1000	Tube and box
UMW BTA16-600CWRG	BTA16-600CW	TO-220A	1000	Tube and box
UMW BTA16-800BWRG	BTA16-800BW	TO-220A	1000	Tube and box
UMW BTA16-800CWRG	BTA16-800CW	TO-220A	1000	Tube and box
UMW BTA16-600SWRG	BTA16-600SW	TO-220A	1000	Tube and box
UMW BTA16-800SWRG	BTA16-800SW	TO-220A	1000	Tube and box



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.