


Bridge Rectifier Diode 整流桥

■Features 特点

Glass passivated chip junction 玻璃钝化结
High surge current capability 高浪涌电流能力
Reflow Solder Temperature 220℃ 回流焊温度 220 度
Package 封装: ABS



■Maximum Rating 最大额定值

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	ABS1 -AAF	ABS2 -AAF	ABS4 -AAF	ABS6 -AAF	ABS8 -AAF	ABS10 -AAF	Unit 单位
Peak Reverse Voltage 反向峰值电压	V_{RRM}	100	200	400	600	800	1000	V
DC Reverse Voltage 直流反向电压	$V_{R(DC)}$	100	200	400	600	800	1000	V
RMS Reverse Voltage 反向电压均方根值	$V_{R(RMS)}$	70	140	280	420	560	700	V
Forward Rectified Current 正向整流电流	I_F	1						A
Peak Surge Current 峰值浪涌电流	I_{FSM}	35						A
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	72						$^{\circ}\text{C}/\text{W}$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	$150^{\circ}\text{C}, -55\text{to}+150^{\circ}\text{C}$						

■Electrical Characteristics 电特性

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	Min 最小值	Typ 典型值	Max 最大值	Unit 单位	Condition 条件
Forward Voltage 正向电压降	V_F		1.1		V	$I_F=1\text{A}$
Reverse Current ($T_A=25^{\circ}\text{C}$) 反向漏电流($T_A=125^{\circ}\text{C}$)	I_R			5 100	μA	$V_R=V_{RRM}$
Diode Capacitance 二极管电容	C_D		13		pF	$V_R=4\text{V}, f=1\text{MHz}$

■ Typical Characteristic Curve 典型特性曲线




Figure 1: Forward Current Derating Curve




Figure 2: Peak Forward Surge Current




Figure 3: Instantaneous Forward Characteristics




Figure 4: Reverse Leakage Characteristics





Figure 5: Junction Capacitance Characteristics

■Dimension 外形封装尺寸



UNIT		A	C	D	E	H _E	d	e	L	L ₁	a	∠
mm	max	1.5	0.22	5.2	4.5	6.4	4.2	0.7	0.95	0.6	0.2	7°
	min	1.3	0.15	4.9	4.2	6.0	3.8	0.5				
mil	max	59	8.7	205	177	252	165	28	37	24	8	
	min	51	5.9	193	166	236	150	20				