


1.Features

- $V_{DS(V)} = -60V$
- $I_D = -7A$
- $R_{DS(ON)} < 55m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 65m\Omega (V_{GS} = -4.5V)$

2.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

SOT-223



3.Maximum ratings ($T_A = 25^\circ C$ unless otherwise noted)

Parameter		Symbol	Maximum	Units
Drain-Source Voltage		V_{DS}	-60	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 150^\circ C$)	$T_C = 25^\circ C$	I_D	-7 ^a	A
	$T_C = 70^\circ C$		-5.2	
	$T_A = 25^\circ C$		-4.8 ^b	
	$T_A = 70^\circ C$		-4.1	
Pulsed Drain Current		I_{DM}	-25	
Avalanche Current Pulse	L = 0.1 mH	I_{AS}	-4.5	mJ
Single Pulse Avalanche Energy		E_{AS}	10.1	
Continuous Source-Drain Diode Current	$T_C = 25^\circ C$	I_S	6.9 ^a	A
	$T_A = 25^\circ C$		3.5 ^b	



Maximum Power Dissipation	$T_C=25^{\circ}\text{C}$	P_D	10.4 ^a	W
	$T_C=70^{\circ}\text{C}$		6.6 ^a	
	$T_A=25^{\circ}\text{C}$		2.1 ^b	
	$T_A=70^{\circ}\text{C}$		1.1 ^b	
Storage Temperature Range		T_J, T_{STG}	-55 to 150	$^{\circ}\text{C}$

4. Thermal Resistance Rating

Parameter		Symbol	Typ	Max	Units
Maximum Junction-to-Ambient ^b	Steady-State	R_{thJA}	33	40	$^{\circ}\text{C/W}$
Maximum Junction-to-Case	Steady-State	R_{thJC}	0.98	1.2	$^{\circ}\text{C/W}$

Notes:

a. Based on $T_C=25^{\circ}\text{C}$.

b. Surface mounted on 1" x 1" FR4 board.



5. $T_J=25^{\circ}\text{C}$ unless otherwise specified

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static						
Drain-Source Breakdown Voltage	V_{DS}	$V_{GS}=0\text{V}, I_D=-250\mu\text{A}$	-60			V
V_{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	$I_D=-250\mu\text{A}$		68		mV/ $^{\circ}\text{C}$
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$			-5.2		
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu\text{A}$	-1		-2.5	V
Gate-Source Leakage	I_{GSS}	$V_{DS}=0\text{V}, V_{GS}=\pm 20\text{V}$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=-60\text{V}, V_{GS}=0\text{V}$			-1	μA
		$V_{DS}=-60\text{V}, V_{GS}=0\text{V}, T_J=55^{\circ}\text{C}$			-10	
On-State Drain Current ^a	$I_{D(ON)}$	$V_{DS}=-5\text{V}, V_{GS}=-10\text{V}$	-25			A
Drain-Source On-State Resistance ^a	$R_{DS(ON)}$	$V_{GS}=-10\text{V}, I_D=-3\text{A}$		55		m Ω
		$V_{GS}=-4.5\text{V}, I_D=-2\text{A}$		65		
Forward Transconductance ^a	g_{FS}	$V_{DS}=-15\text{V}, I_D=-5\text{A}$	20			S
Dynamic^b						
Input Capacitance	C_{iss}	$V_{DS}=-25\text{V}, V_{GS}=0\text{V}, f=1\text{MHz}$		1500		pF
Output Capacitance	C_{oss}			200		
Reverse Transfer Capacitance	C_{rss}			150		
Total Gate Charge	Q_g	$V_{DS}=-30\text{V}, V_{GS}=-10\text{V}$ $I_D=-5\text{A}$		38	56	nC
				19	30	
Gate Source Charge	Q_{gs}	$V_{DS}=-30\text{V}, V_{GS}=-4.5\text{V}$		9		
Gate Drain Charge	Q_{gd}			10		
Gate Resistance	R_g	$f=1\text{MHz}$		5.2		Ω
Turn-On DelayTime	$t_{D(on)}$	$V_{DD}=-2\text{V}, R_L=2\Omega$ $I_D \leq -5\text{A}, V_{GEN}=-10\text{V}$ $R_g=1\Omega$		10	15	ns
Rise Time	t_r			7	15	
Turn-Off DelayTime	$t_{D(off)}$			70	110	
Fall Time	t_f			40	60	



Drain-Source Body Diode Characteristics						
Continuous Source-Drain Diode Current	I_S	$T_C=25^{\circ}\text{C}$			-6.9	A
Pulse Diode Forward Current	I_{SM}				-15	A
Body Diode Voltage	V_{SD}	$I_S=-3\text{A}$		-1	-1.5	V
Body Diode Reverse Recovery Time	t_{rr}	$I_F=-5\text{A}, dI/dt=10\text{A}/\mu\text{s}$ $T_J=25^{\circ}\text{C}$		45	68	ns
Body Diode Reverse Recovery Charge	Q_{rr}			59	120	nC
Reverse Recovery Fall Time	t_a			29		ns
Reverse Recovery Rise Time	t_b			16		ns

Notes:

- a. Pulse test; pulse width $\leq 300 \mu\text{s}$, duty cycle $\leq 2\%$.
- b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.



6.1 Typical Characteristics




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: Transfer Characteristics




Figure 4: Transconductance




Figure 5: On-Resistance vs. Drain Current




Figure 6: Capacitance



6.2 Typical Characteristics




Figure 7: Gate Charge




Figure 8: On-Resistance vs. Gate-to-Source Voltage




Figure 9: Source-Drain Diode Forward Voltage




Figure 10: On-Resistance vs. Gate-to-Source Voltage




Figure 11: Single Pulse Avalanche Current Capability vs. Time




Figure 12: Drain-Source Breakdown Voltage vs. Junction Temperature



6.3 Typical Characteristics




Figure 13: Threshold Voltage




Figure 14: Max. Drain Current vs. Case Temperature





Figure 15: Power Derating, Junction-to-Case



* $V_{GS} > \text{minimum } V_{GS} \text{ at which } R_{DS(ON)} \text{ is specified}$

Figure 16: Safe Operating Area, Junction-to-Case





Figure 17: Normalized Thermal Transient Impedance, Junction-to-Case



7.SOT-223 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	b	b1	c	D	E	E1	e	L	θ
Min	-	0.020	1.500	0.660	2.900	0.230	6.300	6.700	3.300	2.300	0.750	0°
Max	1.800	0.100	1.700	0.840	3.100	0.350	6.700	7.300	3.700	BSC	-	10°



8.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW NTF2955T1G	SOT-223	2500	Tape and reel



9.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.