






REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2011/10/31



RECOMMENDED PCB LAYOUT
TOLERANCES ±0.05


—NOTES—

- Electrical:
Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.
 - Mechanical:
MATE AND UNMATE FORCE:
MATE FORCE:4.5kg MAX
UNMATE FORCE:0.5kg MIN
Durability:1500cycles MIN.
 - Environment:
Operating Temperature:−25°to+85°.
 - FINISH:
TERMINAL: GOLD Plated Over NICKEL
Contact area,TIN ON
SOLDER TAIL AREA& TIN
Plated ALL Over NICKEL.
Shell: SPCC WITH NICKEL&GOLD Plated.
- 5.COLOR:
HOUSING:BLACK.



序号	DIM A	料号
1	2.65H	5001B-TF265-042
2	2.85H	5001B-TF285-043
3	3.00H	5001B-TF300-044
4	3.35H	5001B-TF335-045
5	3.75H	5001B-TF375-046
6	5.20H	5001B-TF520-047

Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1



GENERAL TOLERANCE			DWG NO.		APPD:	WIND	Scale	1:1
X.±0.45		x.*±5°	Title	短型 T CARD 无侦测	CHKD:		UNIT	mm
.X±0.35		.x*±2°			DR:			
.XX±0.25		.xx*±1°	Part NO.	5001B-TF265-042	Date	2012/08/10		
.XXX±0.15		.xxx*±0.5°			东莞市文章济美电子有限公司			
SHEET	1/1							