

1.Description

The UMW MOC308x series devices are optocouplers composed of a GaAs infra-red light emitting diode and a singlecrystal silicon chip random phase photoelectric bidirectional thyristor.


2.Application

- Solenoid valve / Valve control
- Lighting control
- Static power switches
- AC motor drives
- Electromagnetic contactors (or Relay switches)
- Solid-state relays (SSR)

3.Features

- Peak breakdown voltage 800V
- High isolation voltage between input and output($V_{ISO}=5000\text{ Vrms}$)
- Zero-voltage crossing
- Compact DIP (Dual In-line Package) housing
- Compliant with RoHS standards
- UL approved: UL1577, file No.E547318

4.Pinning information





5. Absolute Maximum Ratings

Parameter		Symbol	Value	Unit
Input				
Forward Current		I _F	60	mA
Backward Voltage		V _R	6	V
Power Dissipation		P _D	100	mW
Power dissipation Derating factor (above Ta=85°C)			3.8	mW/°C
Output				
Off-state output terminal voltage	UMW MOC308x	V _{DRM}	800	V
Peak repetitive surge current (pw=100μs,120pps)		I _{TSM}	1	A
On-state current (root mean square value)		I _{T(RMS)}	100	mA
Power Dissipation		P _C	300	mW
Power dissipation Derating factor (above Ta=85°C)			7.6	mW/°C
Total Power Dissipation		P _{TOT}	330	mW
Isolation Voltage		V _{ISO}	5000	V
Operating Temperature		T _{OPR}	-55 to 110	°C
Storage Temperature		T _{STG}	-55 to 125	°C
Soldering Temperature (10s)		T _{SOL}	260	°C

Notes:

Conduct AC test at 40% ~60% relative humidity. At this time, pins 1, 2 and 3 are short-circuited, and pins 4, 5 and 6 are short-circuited.



6. Electro-optical Characteristics ($T_A=25^\circ\text{C}$)

Parameter		Symbol	Conditions	Min	Typ	Max	Units
Input							
Forward Voltage		V_F	$I_F=30\text{mA}$			1.5	V
Back current		I_R	$V_R=6\text{V}$			10	μA
Output							
Off-state peak current	UMW MOC308x	I_{DRM1}	$V_{\text{DRM}}=\text{Rated } V_{\text{DRM}}, I_F=0\text{mA}$			500	nA
Peak on-state voltage		V_{TM}	$I_{\text{TM}}=100\text{mA peak}, I_F=\text{Rated } I_{\text{FT}}$			3	V
Critical rate of rise of off-state voltage		dv/dt	$V_{\text{PEAK}}=\text{Rated}$	600			V/ μs
Blocking voltage		V_{Inh}	$I_F=\text{Rated } I_{\text{FT}}$			20	V
Leakage current in blocking state		I_{DRM2}	$I_F=\text{Rated } I_{\text{FT}}$ $V_{\text{DRM}}=\text{Rated Value}$ $V_{\text{DRM}}, \text{Off-State}$			500	μA
Transfer Characteristics							
LED trigger current	UMW MOC3081	I_{FT}	Main terminal Voltage =3V			15	mA
	UMW MOC3082					10	mA
	UMW MOC3083					5	mA
Maintain current		I_H			280		μA




7.1Typical Characteristic

Figure 1: LED Forward Voltage vs. Forward Current	Figure 2: On-State Characteristics
Figure 3: Trigger Current vs. Ambient Temperature	Figure 4: LED Current Required to Trigger vs. LED Pulse Width
Figure 5: dv/dt vs. Temperature	Figure 6: Leakage Current, IDRM vs. Temperature




7.2Typical Characteristic





8.Static dv/dt test circuit and waveform



The high voltage pulse applied to the output end of the device under test through the RC circuit is set to the desired V_{PEAK} value. LED current does not need to be added. Waveform V_T is monitored with X100 probe. By adjusting the R_{TEST} value, dv/dt (slope) increases until the device under test is observed to be triggered (waveform collapse). Dv/dt then drops until the device under test stops being triggered. At this time, dv/dt can be calculated by recording the value of τRC .


$$dv/dt = \frac{0.632 \times 800}{\tau RC} = \frac{505}{\tau RC}$$

For example, the voltage peak of UMW MOC308x series $V_{PEAK}=800V$. Then the dv/dt value can be calculated as follows:

$$dv/dt = \frac{0.632 \times 800}{\tau RC} = \frac{505}{\tau RC}$$



9.DIP-6/SOP-6 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	B	B1	B2	b	c	D	D1	E
Min	6.45	7.45	0.2	8.7	7.07	1.625	1.595	3.45	4.2	7.45	6.45	0.76
Max	6.55	7.75	(typ.)	9.1	7.14	(typ.)	1.655	3.55	4.4	7.75	6.55	(typ.)

Symbol	E1	F
Min	10.0	3.45
Max	10.4	3.55



10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW MOC3081M	MOC3081	DIP-6	3250	Tape and reel
UMW MOC3082M	MOC3082	DIP-6	3250	Tape and reel
UMW MOC3083M	MOC3083	DIP-6	3250	Tape and reel
UMW MOC3083SM	MOC3083	SOP-6	1000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.