






REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2019/05/29



SIM PIN ASSIGNMENT	
PIN	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



RECOMMEND PCB LAYOUT
TOLERANCE: $\pm 0.05\text{mm}$ (TOP VIEW)

MATERIALS

1. HOUSING : LCP (UL 94V-0), BLACK.
2. TERMINAL : PHOSPHOR BRONZE, GOLD FLASH PLATED, NICKEL UNDERPLATING.
3. SHELL : STAINLESS STEEL, GOLD FLASH PLATED ON PAD AREA, NICKEL UNDERPLATING.

SPECIFICATION






1. CURRENT RATING : 0.5mA AC/DC MAX.
2. VOLTAGE RATING : 125V AC/DC.
3. CONTACT RESISTANCE : 100m Ω MAX.
4. INSULATION RESISTANCE : 1000M Ω Min, AT 500V DC.
5. AMBIENT TEMPERATURE : -20°C TO +60°C

GENERAL TOLERANCE		DWG NO.			APPD:	WIND	Scale	1:1
X. ± 0.45	x. $\pm 5^\circ$	Title	NANO SIM 6PIN 有柱 1.35H		CHKD:		UNIT	mm
.X ± 0.35	.x $\pm 2^\circ$	Part NO.	5001B-SIM135-116		DR:			
.XX ± 0.25	.xx $\pm 1^\circ$		Date		2019/05/29			
.XXX ± 0.15	.xxx $\pm 0.5^\circ$							
SHEET	1/1							

东莞市文章济美电子有限公司

REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2016/05/29

PULL OUT DIRECTION
→



PACKAGE

- SIZE :
REEL : φ330 x 24 mm
CARTON : 345 x 345 x 310 mm (LxWxH)
- QUANTITY :
1,800 PCS / REEL
10 REEL / CARTON = 18,000 PCS

GENERAL TOLERANCE		DWG NO.			APPD:	WIND	Scale	1:1
X. ⁺ 0.45	x. ⁺ 5°	Title	NANO SIM 6PIN 有柱 1.35H 包装图		CHKD:			
.X±0.35	.x [±] 2°				DR:			
.XX±0.25	.xx [±] 1°	Part NO.	5001B-SIM135-116		Date	2016/05/29		
.XXX±0.15	.xxx [±] 0.5°							
SHEET	1/1							

东莞市文章济美电子有限公司