



REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2014/03/29



NOTES:

- 1.ELECTRICAL PERFORMANCES:
 - 1-1. RATING CURRENT: 0.5A.
 - 1-2. RATING VOLTAGE: 50V AC.
 - 1-3. CONTACT RESISTANCE: 50mΩ. MAX.
 - 1-4. INSULATION RESISTANCE: 1000MΩ. MIN.
 - 1-5. DIELECTRIC WITHSTANDING VOLTAGE: 250V AC FOR 1 MINUTE.
- 2.MECHANICAL PERFORMANCE:
 - 2-1. DURABILITY: 5000TIMES.
 - 2-2. NORMAL FORCE AT MATING POSITION : 0.2N MIN.
 - 2-3. OPERATION TEMPERATURE: -35℃~+85℃.
- 4.EMPHASIS SIZE MARK"*

PIN No.	DESCRIPTION
C1	VCC (SUPPLY VOLTAGE)
C2	RST (RESET SIGNAL)
C3	CLK (CLOCK SIGNAL)
C4	RESERVED
C5	GND
C6	VPP (VARIABLE SUPPLY VOLTAGE)
C7	I/O (DATA INPUT/OUTPUT)
C8	RESERVED
SW	DETECT SWLTC




ITEM	DESCRIPTION	QUANTITY	SCHEMATIC		
			CARD INSERTION STATE	DETECT SWITCH CIRCUIT STATE	SCHEMATIC
CARD MATED	CLOSED	(D.S.) → D.C.			
CARD UNMATED	OPENED	(D.S.) ← D.C.			

ITEM	DESCRIPTION	QUANTITY	GENERAL TOLERANCE			REMARK	
			APPD:	WIND	Scale		
③	SHELL	1	STAINLESS STEEL	NICKEL 50μ" MIN. PLATING OVER ALL GOLD PLATING AT SOLDER AREA			
②	CONTACT	1	COPPER ALLOY	GOLD PLATING AT CONTACT AREA AND SOLDER AREA NICKEL 50μ" MIN. PLATING OVER ALL			
①	HOUSING	1	THERMOPLASTIC UL94V-0 COLOR:BLACK				
ITEM	DESCRIPTION	QUANTITY	MATERIAL	FINISH			


GENERAL TOLERANCE		DWG NO.	Title	9PIN MICRO SIM CARD H1.50 (防爆PIN)	APPD:	WIND	Scale	1:1
X.±0.45	x.±5°							
X.±0.35	.x.±2°				CHKD:			
.XX±0.25	.xx.±1°		Part NO.	5001B-SIM150-167	DR:			
.XXX±0.15	.xxx.±0.5°				Date	2014/03/29		
SHEET	1/2							

东莞市文章济美电子有限公司




NOTES

1. NUMBER OF CONNECTORS: 1300PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 10400PCS/CARTON



GENERAL TOLERANCE		DWG NO.			APPD:	WIND	Scale	1:1
X.±0.45	x.±5°	Title	9PIN MICRO SIM CARD H1.50	(防爆PIN)	CHKD:		UNIT	mm
.X±0.35	.x.±2°				DR:			
.XX±0.25	.xx.±1°	Part NO.	5001B-SIM150-167		Date	2014/03/29		
.XXX±0.15	.xxx.±0.5°							
SHEET	2/2							

东莞市文章济美电子有限公司