





技术要求:

1. 塑件材料: PA66 (UL-94V-0)

2. 接触件: 黄铜镀锡

3. 接触电阻: $\leq 10\text{m}\Omega$

4. 绝缘电阻: $\geq 100\text{M}\Omega$

5. 额定电压: 250V AC DC

6. 额定电流: 2.0A AC DC

7. 耐压: 能承受 1000V AC/Minute

8. 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 时间 $2.5 \pm 0.5\text{s}$

10. 铅和镉等六大有害物质含量要符合环保要求。

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PIN number variable size comparison table

PART NO	PIN	A	B	C
JXT-PH2.0-2PZZ	2	2.00	6.00	4.50
JXT-PH2.0-3PZZ	3	4.00	8.00	6.00
JXT-PH2.0-4PZZ	4	6.00	10.00	7.50
JXT-PH2.0-5PZZ	5	8.00	12.00	9.00
JXT-PH2.0-6PZZ	6	10.00	14.00	10.50
.....				
JXT-PH2.0-20PZZ	20	38.00	42.00	25.50

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀 底镍 30u"MIN, 再 镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.* ±5°	PART NO.	TITLE:	
.XX±0.20	X.* ±1°	JXT-PH2.0-NPZZ	PH2.0MM 直针	
.XXX±0.10	X.XX* ±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olivia		
MATERILA	— — —	APPD: Ava		
FINISH	— — —		SCALE	SHEET
			N:A	1/1