

SOT-23-6L Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=30V$
- $I_D=3.4A$
- $R_{DS(on)}@V_{GS}=10V < 60m\Omega$
- $R_{DS(on)}@V_{GS}=4.5V < 70m\Omega$
- Trench Power LV MOSFET technology
- Voltage controlled small signal switch
- Fast Switching Speed

Drain-source Voltage
30 V
Drain Current
3.4 Ampere


Applications

- Battery operated systems
- Load switch
- Uninterruptible power supply

Mechanical Data

- Case: SOT-23-6L
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23-6L	R1	0.008	3000	30000	180000	7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	30
Gate-source Voltage	V_{GS}	V	± 12
Drain Current	I_D	A	3.4
Pulsed Drain Current	I_{DM}	A	20
Total Power Dissipation @ $T_A=25^{\circ}C$	P_D	W	1.15
Thermal Resistance Junction-to-Ambient @ Steady State	$R_{\theta JA}$	$^{\circ}C / W$	108
Junction and Storage Temperature Range	T_J, T_{STG}	$^{\circ}C$	-55 ~+150



● Static Parameter Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	V	30	—	—
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=30V, V_{GS}=0V$	μA	—	—	1.0
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 12V, V_{DS}=0V$	nA	—	—	± 100
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	V	0.5	1.0	1.5
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS}=10V, I_D=3.4A$	m Ω	—	46	60
		$V_{GS}=4.5V, I_D=3A$		—	53	70
		$V_{GS}=2.5V, I_D=2A$		—	65	90
Diode Forward Voltage	V_{SD}	$I_S=3.4A, V_{GS}=0V$	V	—	0.75	1.0
Maximum Body-Diode Continuous Current	I_S	—	A	—	—	3.4

● Dynamic Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C_{iss}	$V_{DS}=15V$ $V_{GS}=0V$ $f=1.0MHz$	pF	—	380	—
Output Capacitance	C_{oss}			—	46	—
Reverse Transfer Capacitance	C_{rss}			—	31	—

● Switching Parameters (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Total Gate Charge	Q_g	$V_{GS}=10V$ $V_{DS}=15V$ $I_D=3.4A$	nC	—	10	—
Gate-Source Charge	Q_{gs}			—	1	—
Gate-Drain Charge	Q_{gd}			—	1.6	—
Turn-on Delay Time	$t_{D(on)}$	$V_{GS}=10V, V_{DD}=15V$ $I_D=3.4A, R_{GEN}=3.0\Omega$	ns	—	2.5	—
Turn-on Rise Time	t_r			—	2	—
Turn-off Delay Time	$t_{D(off)}$			—	18	—
Turn-off fall Time	t_f			—	3	—

● Package Outline Dimensions (SOT-23-6L)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.80	3.00	0.110	0.118
B	2.60	3.00	0.102	0.118
C	0.93	0.97	0.037	0.038
D	0.41		0.016	
E	1.50	1.70	0.059	0.067
F	0.11	0.19	0.004	0.007
G	-	0.10	-	0.004
H	0.40	-	0.016	-
J	1.00	1.20	0.035	0.057

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.65	0.75	0.026	0.03
K	0.95	1.05	0.038	0.043
M	-	1.40	-	0.055
N	-	0.35	-	0.014
X	-	0.95	-	0.037
Y	-	2.30	-	0.090
L	-	2.50	-	0.098