




REV.	Q'TY	ECN. NO.	APR.	DATE



**SPECIFICATIONS**

Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Phosphor bronze  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PM1.27-2-01P-S	2*1	0.00	1.27
PM1.27-2-02P-S	2*2	1.27	2.54
PM1.27-2-03P-S	2*3	2.54	3.81
PM1.27-2-04P-S	2*4	3.81	5.08
PM1.27-2-05P-S	2*5	5.08	6.35
PM1.27-2-06P-S	2*6	6.35	7.62
PM1.27-2-07P-S	2*7	7.62	8.89
PM1.27-2-08P-S	2*8	8.89	10.16
PM1.27-2-09P-S	2*9	10.16	11.43
.....	.....	.....	.....
PM1.27-2-50P-S	2*50	(PIN-1)x1.27	(PIN)x1.27



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 1.27FH H4.3 2xNPin SMT U# PC4.8 PB4.6 6T	
.X $\pm 0.3$	X.* $\pm 5^\circ$	CHK.	Jack	DWG NO. PM1.27-2-NP-S	
.XX $\pm 0.2$	.X* $\pm 1$	DRA.	Can	CUSTOMER DRAWING	
.XXX $\pm 0.1$	.XX* $\pm 0.5$	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A