




SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
 (260 $^{\circ}$ C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
PM2.00-2-01P-Z	2*1	0.00	2.00
PM2.00-2-02P-Z	2*2	2.00	4.00
PM2.00-2-03P-Z	2*3	4.00	6.00
PM2.00-2-04P-Z	2*4	6.00	8.00
PM2.00-2-05P-Z	2*5	8.00	10.00
PM2.00-2-06P-Z	2*6	10.00	12.00
PM2.00-2-07P-Z	2*7	12.00	14.00
PM2.00-2-08P-Z	2*8	14.00	16.00
PM2.00-2-09P-Z	2*9	16.00	18.00
.....
PM2.00-2-40P-Z	2*40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.0FH H6.35 2xnPin 180 μ Y \sharp PC2.8 6T	
.X \pm 0.3	X.* \pm 5'	CHK.	Jack	DWG NO. PM2.00-2-NP-Z	
.XX \pm 0.2	.X* \pm 1	DRA.	Can	PROJ.	CUSTOMER DRAWING
.XXX \pm 0.1	.XX* \pm 0.5	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A