

General Description

The HSS5N04A is the high cell density trenched N-ch MOSFETs, which provides excellent $R_{DS(on)}$ and efficiency for most of the small power switching and load switch applications.

The HSS5N04A meet the RoHS and Green Product requirement with full function reliability approved.


Product Summary

V_{DS}	40	V
$R_{DS(ON),typ}$	30	m Ω
I_D	4.9	A

Features

- Green Device Available
- Super Low Gate Charge
- Excellent $C_{dv/dt}$ effect decline
- Advanced high cell density Trench Technology

SOT-23S Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	40	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_A=25^\circ\text{C}$	Continuous Drain Current ¹	4.9	A
$I_D@T_A=70^\circ\text{C}$	Continuous Drain Current ¹	3.0	A
I_{DM}	Pulsed Drain Current ²	20	A
$P_D@T_A=25^\circ\text{C}$	Total Power Dissipation ¹	0.72	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ¹	---	175	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	80	$^\circ\text{C/W}$

Note :

1..Surface mounted on 1" x 1" FR4 board, $t \leq 10\text{sec}$

2.Pulse width limited by maximum junction temperature



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	40	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ¹	$V_{GS}=10V, I_D=5A$	---	30	40	$m\Omega$
		$V_{GS}=4.5V, I_D=3A$	---	38	50	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	1.0	1.5	2.3	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=40V, V_{GS}=0V, T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=40V, V_{GS}=0V, T_J=55^\circ\text{C}$	---	---	10	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance ¹	$V_{DS}=5V, I_D=4A$	---	16	---	S
Q_g	Total Gate Charge	$V_{DS}=20V, V_{GS}=10V, I_D=2A$	---	10	---	nC
Q_{gs}	Gate-Source Charge		---	2.6	---	
Q_{gd}	Gate-Drain Charge		---	3	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=20V, V_{GS}=10V, R_G=3\Omega, R_L=1\Omega$	---	11	---	ns
T_r	Rise Time		---	7.6	---	
$T_{d(off)}$	Turn-Off Delay Time		---	30	---	
T_f	Fall Time		---	12.5	---	
C_{iss}	Input Capacitance	$V_{DS}=20V, V_{GS}=0V, f=1\text{MHz}$	---	445	---	pF
C_{oss}	Output Capacitance		---	60	---	
C_{rss}	Reverse Transfer Capacitance		---	38	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_S=1A, T_J=25^\circ\text{C}$	---	---	1.2	V

Note :

1.Pulse test: pulse width $\leq 300\mu s$, duty $\leq 2\%$

2.Guaranteed by design, not subject to production testing



Typical Characteristics




Fig.1 Output Characteristic




Fig.2 Transfer Characteristic




Fig.3 On-Resistance vs. Drain Current




Fig.4 Body Diode Characteristic




Fig.5 Gate-Charge Characteristic





Fig.6 Capacitance Characteristic



Ordering Information

Part Number	Package code	Packaging
HSS5N04A	SOT-23S	3000/Tape&Reel


SOT-23S Package Outline



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
C	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°



HSS5N04A TOP Marking



Part Number