SS3H9-E3/57T
Schottky Rectifier Diodes

Features

SMC

- Guard Ring Die Construction for Transient Protection
- Low Power Loss, High Efficiency
- Surge Overload Rating to 100A Peak
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Application
- Lead Free Finish/RoHS Compliant
- Green Molding Compound (No Halogen and Antimony)

Mechanical Data

- Case: SMC
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Lead Free Plating (Matte Tin Finish). Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band or Cathode Notch
- Weight: 0.21 grams (approximate)

Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
SS3H9-E3/57T	SMC	B390C	3000

Maximum Ratings (Ta=25°C unless otherwise noted)

Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Item	Symbol	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	90	V
Maximum RMS Voltage	V_{RMS}	36	V
Average Rectified Output Current @ Tj = 90°C	I_O	3.0	A
Surge(Non-repetitive)Forward Current	I_{FSM}	100	A
Junction Temperature	T_J	-55~+125	℃
Storage Temperature	T_{STG}	-55 ~ +150	℃
Typical Thermal Resistance Junction to Terminal	$R_{\theta JT}$	10	°C/W

Electrical Characteristics (Ta=25°C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Forward Voltage Drop	V_F	- -	- -	0.79 0.69	V	I_F = 3.0A, T_A = 25°C I_F = 3.0A, T_A = 100°C
Leakage Current (Note 1)	I_R	- -	- -	0.5 20	mA	@ Rated V_R, T_A = 25°C @ Rated V_R, T_A = 100°C
Total Capacitance	C_T	-	-	100	pF	V_R = 4V, f = 1MHz

Notes: 1. Short duration pulse test used to minimize self-heating effect.

Typical Characteristics



Fig. 1 Typical Forward Characteristics



Fig. 2 Total Capacitance vs. Reverse Voltage



Fig. 3 Forward Current Derating Curve



Fig. 4 Max Non-Repetitive Peak Forward Surge Current

Package Outline Dimensions

SMC



Dimensions in inches and (millimeters)

Attention

■ Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

■ HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

■ Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could
give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.