



SPECIFICATION

Poles:2-12

Voltage rating:AC,DC 250V

Current rating:AC,DC,7A

Withstand voltage:1500V AC/min.

Insulation resistance:1000M Ω /min.

Temperature range:-25℃ $\sim$ +85℃

Applicable PC board thickness:0.031"~0.063"(0.8~1.6mm)

Contact resistance:Initial value/10m Ω max.

After environmental
testing/20m Ω max.

Material:Nylon66 UL94V-2

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:

DATE:

Ckmtw 深圳市灿科盟实业有限公司
CHANKLEMENT INDUSTRYCO., LTD

CHECKED:

DATE:

TITLE:

5557HP-1*5P 公壳

DRAWN:

DATE:

CLIENT P/N C169040

LYF

2008-04-07

UNIT	mm	SCALE	free		
FILE NO.	Ckmtw-5557-0002	REV.	A	DGHW	