







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

PZ/N	PZIN	DIM.A	DIM.B
254-2*3PZ	2*3	5.08	7.62
254-2*4PZ	2*4	7.62	10.16
254-2*5PZ	2*5	10.16	12.70
254-2*6PZ	2*6	12.70	15.24
254-2*7PZ	2*7	15.24	17.78
254-2*8PZ	2*8	17.78	20.32
254-2*9PZ	2*9	20.32	22.86
254-2*10PZ	2*10	22.86	25.40
254-2*12PZ	2*12	27.94	30.48
254-2*13PZ	2*13	30.48	33.02
254-2*14PZ	2*14	33.02	35.56
254-2*15PZ	2*15	35.56	38.10
254-2*16PZ	2*16	38.10	40.64
254-2*17PZ	2*17	40.64	43.18
254-2*18PZ	2*18	43.18	45.72
254-2*20PZ	2*20	48.26	50.80
254-2*22PZ	2*22	53.34	55.88
254-2*25PZ	2*25	60.96	63.50
254-2*30PZ	2*30	73.66	76.20
254-2*32PZ	2*32	78.74	81.28

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.30	X.*±5°	PART NO. 254-2*NPZ	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T		
X.X±0.20	X.X*±2°				
X.XX±0.10	X.XX*±1°				
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	---	CHED:	Olvia		
FINISH	---	APPD:	Ava		SCALE N:A
					SHEET 1/1