


L2-6



电气性能参数:

- 额定负载: DC50V 0.3A
- 接触电阻: 100毫欧以下
- 绝缘电阻: 100兆欧以上
- 耐压: AC 500V
- 力度: 250[±]100gf
- 寿命: 10000次
- 回流焊温度: 255° ± 5°
- 手焊: 350[±]10度

8				
7				
6				
5	CONTACT	PBS STRIP	1	AG PLATEN
4	TERMINAL	BRASS STRIP	4	AG PLATEN OVER Ni PLATEN
3	BASB	PHENOLIC RESIN	1	NATURAL
2	KNOB	POM	1	BLACK
1	FRAME	STEEL STRIP	1	Ni PLATEN
NO.	PARTS	MATERLALS	Q"TY	FINISH

TOLXPANCE UNLESS SPECIFEN				
	WITHIN 1.5mm: ± 0.1mm	A	20190717	初版
OVER 1.5mm: ± 0.2mm	ISSUE	DATE	DESCRIPTIONS OF REVISION	APPD.
MODEL: SK12D07VG3-T			UNIT:mm	DRWG NO:
			SCALE:3:1	DWN. 黃彬 2020.8.25
			CHK"D	张伟 2020.8.25



® 深圳市韩下电子有限公司