








P.C.B Layout(Copper-sided view)



SPECIFICATION

- 1.Rating : DC 30V 0.5A;
- 2.Contact resistance: $\leq 50\text{m}\Omega$;
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 3-25N;
- 6.life test: 5,000 cycles.

Model No.			
PIN	φ2.0	φ2.35	φ2.5

电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk
 V:hooya89

8				TOLERANCE UNLESS SPECIFIED															
7																			
6	COVER	PBT	1		UP TO 5mm: ±0.1	ANGULAR													
5	HOUSING	PBT	1	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY	APPD							
4	PIN	BRASS	1	Ni-Plating	TITLE: DC JACK			UNIT : MM	ROHS	DWN									
3	FLAT PIECE	BRASS	1	Sn-Plating	MODEL: DC-020-2.0			SCALE: 1:1	COMPLIANT	CHK'D									
2	CURVE PIECE	BRASS	1	Sn-Plating	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD							
1	SPRING	STEEL	1	Sn-Plating															
NO.	PART NAME	MATERIAL	QTY	FINISHING															
														PRO.AGL:			REV :A0		