


P.C.B LAYOUT



PIN	φ1.65	φ2.0	φ2.5
APPD.			

					TOLERANCE								
					UNLESS SPECIFIED								
6	DC015 PING	BRASS	1	Ni PLATED	UP TO 5mm: ±0.1	ANGULAR	A0	2018.04.04	初版		GYW		
5	DC012 3#SPRING	SUS/PBS	1	Ag PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
4	DC012 2#CURVE PIECE	BRASS	1	Ag PLATED	TITLE:DC JACK			UNIT : MM	ROHS	DWN			
3	DC012 5#FLAT PIECE	BRASS	1	Ag PLATED	MODEL: DC-012-2.5-PU			SCALE: 4:1	COMPLIANT	CHK'D			
2	DC012 BASE	PHENOLIC RESIN	1	YELLOW	HOOYU ELECTRONIC CO. LTD 皓宇电子有限公司							APPD	
1	DC012 CASE	PBT/PA66	1	BLACK								PRO.AGL:	
NO.	PART	NAME	MATERIAL	QTY	FINISHING								