







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
WV254-N-2x3P	2*3	5.08	7.62
WV254-N-2x4P	2*4	7.62	10.16
WV254-N-2x5P	2*5	10.16	12.70
WV254-N-2x6P	2*6	12.70	15.24
WV254-N-2x7P	2*7	15.24	17.78
WV254-N-2x8P	2*8	17.78	20.32
WV254-N-2x9P	2*9	20.32	22.86
WV254-N-2x10P	2*10	22.86	25.40
WV254-N-2x12P	2*12	27.94	30.48
WV254-N-2x13P	2*13	30.48	33.02
WV254-N-2x14P	2*14	33.02	35.56
WV254-N-2x15P	2*15	35.56	38.10
WV254-N-2x16P	2*16	38.10	40.64
WV254-N-2x17P	2*17	40.64	43.18
WV254-N-2x18P	2*18	43.18	45.72
WV254-N-2x20P	2*20	48.26	50.80
WV254-N-2x22P	2*22	53.34	55.88
WV254-N-2x25P	2*25	60.96	63.50
WV254-N-2x30P	2*30	73.66	76.20
WV254-N-2x32P	2*32	78.74	81.28

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.±0.30	X.°±5°	PART NO. WV254-N-2xNP	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T			
X.X±0.20	X.X°±2°					
X.XX±0.10	X.XX°±1°					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG			
MATERILA	— — —	CHED: Olvia				
FINISH	— — —	APPD: Ava		SCALE	SHEET	
					N:A	1/1