



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Specifications:

Electrical:

- 1.Current Rating
1.5A/contact terminal
- 2.Voltage Rating
30V DC
- 3.Contact Resistance
30 milliohms MAX
- 4.Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.Lnsulation Resistance:
1000MEGA ohms MIN

Mechanical:


- 1.Cnnector Mate and Unmate ForceMate
Mate force:3.75kgf (MAX)
Unmate force:1.02kgf (MIN)
- 2.Terminal Retenion1.2kgf (MIN)

Material:

- 1.Housing:Hing Temperature Tnermaplastics,UL 94V-0 PBT/LCP White/Black
- 2.Contact:Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area;Tin On Solder Talls
- 2.Shell:
Nickel Plating



PCB.WELDING DRAWING (TOLERANCE:±0.05)

Pin Definition			TOLERANCE		PART NO.	
PIN	Signal Name	Describe	.X±0.30	X.*±5°	TITLE:	
1	VBUS	+5V	.XX±0.25	X.X°±1°	USB10.0-H6.3	
2	D-	Neagative Data Channel	.XXX±0.15		DESIGN: Ethan	
3	D+	Positive Data Channel			CHED: Olvia	
4	GND	Ground			APPD: Ava	



深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO.		TITLE:	
USB10.0-H6.3		USB-AF-短体长度 10.0	
DESIGN: Ethan		MANUFACTURE DWG	
CHED: Olvia			
APPD: Ava			
		SCALE	SHEET
		N:A	1/1