


Description:

This N-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=68V, I_D=80A, R_{DS(on)} < 8m\Omega @ V_{GS}=10V$ (Typ: $6.6m\Omega$)
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 5) Excellent package for good heat dissipation.



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
PS008NG-B	S008N-B	TO- 220	50 pcs/Tube

Absolute Maximum Ratings: ($T_C=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	68	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current	80	A
	Continuous Drain Current- $T_C=100^\circ C$	56	
P_D	Power Dissipation	72	W
I_{DM}	Pulsed Drain Current ¹	320	A
E_{AS}	Single pulse avalanche energy ²	206	mJ
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55-+150	$^\circ C$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.7	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	68	$^\circ C/W$

Electrical Characteristics: ($T_c=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	68	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =68V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	2	3.09	4	V
R _{DS(ON)}	Drain-Source On Resistance ³	V _{GS} =10V, I _D =30A	---	6.6	8	m Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =35V, V _{GS} =0V, f=1MHz	---	5389	---	pF
C _{oss}	Output Capacitance		---	262	--	
C _{rss}	Reverse Transfer Capacitance		---	208	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DS} =35V, I _D =30A, R _{ENG} =3 Ω ,V _{GS} =10V	---	21	---	ns
t _r	Rise Time		---	31.5	---	ns
t _{d(off)}	Turn-Off Delay Time		---	47	---	ns
t _f	Fall Time		---	14.7	---	ns
Q _g	Total Gate Charge	V _{GS} =10V, V _{DS} =35V, I _D =30A	---	98	---	nC
Q _{gs}	Gate-Source Charge		---	31	---	nC
Q _{gd}	Gate-Drain “Miller” Charge		---	25	---	nC
Drain-Source Diode Characteristics						
V _{SD}	Diode Forward Voltage	V _{GS} =0V, I _{SD} =30A	---	---	1.2	V
I _S	Continuous Drain Curren	V _D =V _G =0V	---	---	80	A
I _{SM}	Pulsed Drain Current		---	---	320	A
T _{rr}	Reverse Recovery Time	I _F =28A, T _J =25 °C	---	30	---	ns
Q _{rr}	Reverse Recovery Charge	dI/dt=300A/us	---	41.8	---	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : $T_J=25^{\circ}\text{C}$, $V_{DD}=35\text{V}$, $V_G=10\text{V}$, $L=0.5\text{mH}$
3. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 0.5\%$

Typical Characteristics: ($T_c=25^{\circ}\text{C}$ unless otherwise noted)




Figure 1: Power De-rating




Figure 2: Current De-rating




Figure 3: Normalized Maximum Transient Thermal Impedance




Figure 4: Peak Current Capacity




Figure 5: Output Characteristics




Figure 6: Typical Transfer Characteristics




Figure 7: On-resistance vs. Drain Current




Figure 8: Body Diode Characteristics




Figure 9: Gate Charge Characteristics




Figure 10: Capacitance Characteristics




Figure 11: Normalized Breakdown voltage vs. Junction Temperature




Figure 12: Normalized on Resistance vs. Junction Temperature




Figure 13: Normalized Threshold Voltage vs. Junction Temperature




Figure 14: $R_{DS(ON)}$ vs. V_{GS}





Figure 15: Maximum Safe Operating Area

TO-220 Package Information:



UNIT: mm

SYMBOLS	A	A1	A2	b	b1	c	D	D1	D2	E	E1	e
MIN	4.25	1.25	2.35	0.7	1.15	0.45	14.35	8.80	13.05	9.90	7.85	2.540
MAX	4.65	1.35	2.55	0.9	1.75	0.60	15.95	9.50	13.65	10.35	8.85	BSC
SYMBOLS	e1	H1	L	L1	Q	φP						
MIN	5.080	6.30	12.85	2.85	2.70	3.50						
MAX	BSC	6.65	13.50	3.25	2.90	3.70						

Marking Information:

①. Doingter LOGO


②. Date Code(YWWG / R)

Y : Year Code , last digit of the year

WW : Week Code(01-53)

G/R : G(Green) /R(Lead Free)

③. Part NO.

**Previous Version**

Version	Date	Subjects (major changes since last revision)
1.0	2024-10-16	Release of final version

Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes noresponsibility for the consequences of use without consideration for such information nor use beyond it.
 - Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
 - Shenzhen Doingter assumes noresponsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.
-  Is a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013 Shenzhen DoingterSemiconductor Co.,Ltd. Printed All rights reserved.