



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)		
	A	B	C
7700-02B2-TG	2.00	6.00	3.00
7700-03B2-TG	4.00	8.00	3.00
7700-04B2-TG	6.00	10.00	3.00
7700-05B2-TG	8.00	12.00	5.00
7700-06B2-TG	10.00	14.00	7.00
7700-07B2-TG	12.00	16.00	9.00
7700-08B2-TG	14.00	18.00	11.00
7700-09B2-TG	16.00	20.00	13.00
7700-10B2-TG	18.00	22.00	15.00
7700-11B2-TG	20.00	24.00	17.00
7700-12B2-TG	22.00	26.00	19.00
7700-13B2-TG	24.00	28.00	21.00
7700-14B2-TG	26.00	30.00	23.00
7700-22B2-TG	42.00	46.00	39.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	7700-XXB2-TG		版本 REV.	A						
			X.±0.25	X.*±2'			品名 TITLE	PHB弯针			页次 SHEET	1/1				
			.X±0.20	.X'±1'									客户料号 CUTM. NO.	WAFER DIP TYPE		
			.XX±0.15	.XX'±0.5'											核 准 APPROVAL	东莞市高钺达电子科技有限公司
			.XXX±0.10	.XXX'±0.5'												