







SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出

- NOTES:
- MATERIAL:
1-1. Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
1-2. Terminal: Copper Alloy.
1-3. Shell: Stainless Steel.
 - PLATING:
2-1. Contact: Plated 50u" Ni Overall Contact Au 1u",
2-2. Shell: Plated 50u" Ni Overall, PAD Au 1u"
 - SPECIALITY:
3-1. Current Rating :0.5mA AC/DC max.
3-2. Voltage Rating :125V AC/DC
3-3. Ambient Temperature Range : -20°C~+60°C
3-4. Storage Temperature Range : -40°C~+70°C
3-5. Ambient Humidity Range :95% R.H. Max.
3-6. Contact Resistance:100mΩ max.
3-7. Insulation Resistance:1000MΩ min./500VDC
3-8. Mating Cycles:10,000 Insertions
3-9. Reflow peak temp.:260°C ±5°C, 3~5 S
3-10. Mating Cycles:3,000 Insertions Min

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMENDED PCB LAYOUT


PATTERN PROHIBITION AREA

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±3°	PART NO.	TITLE: NANO-SIM 卡座		
.XX±0.20	X.X°±2°	NANO SIM 6P 1.35H PULL	6Pin 1.35H 有定位柱		
.XXX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---			SCALE N:A	SHEET 1/2



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES

1. NUMBER OF CONNECTORS:**1800PCS/REEL**
2. LEAD TAPE LENGTH



3. QUANTITY: **18000PCS/CARTON**
4. WEIGHT :
 - 3.1 NET WEIGHT : Kg
 - 3.2 GROSS WEIGHT : Kg



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±3°	PART NO. NANO SIM 6P 1.35H PULL	TITLE: NANO-SIM 卡座	
.XX±0.20	X.X°±2°		6Pin 1.35H 有定位柱	
.XXX±0.10			MANUFACTURE DWG	
UNITS	mm	DESIGN:	Ethan	SCALE N:A
MATERILA	---	CHED:	Olvia	
FINISH	---	APPD:	Ava	
				SHEET 2/2