



This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.


Customer Drawing





15 POSITION FEMALE



26,44,62 POSITION FEMALE




RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05MM




Dimensions



Positions	A	B	D	E	F	G	H
15	30.81	24.99	16.33	2.29	19.20	1.145	7.04
26	39.20	33.30	24.70	2.29	27.70	1.145	6.88
44	53.05	47.04	38.40	2.29	41.10	1.145	6.88
62	69.40	63.50	54.80	2.41	57.30	1.205	7.00



78 POSITION MALE/FEMALE



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05MM



REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	04/14/08	IP
2	HK--	Update the Drawing	10/24/12	IP
3	HK--	Update the Drawing	07/23/13	IP
4	HK--	Add soldering tail length	06/25/15	IP
5	HK--	Add Dimension 6.8	12/08/15	IP
6	HK--	Add Pin#1 in the drawing	05/17/19	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" Tin over 50u" min nickel over 50u" min Copper
BODY : Glass-Filled Thermoplastic PBT, UL94V-0 , Black
CONTACTS : Copper alloy
Gold flash over 50u" nickel on mating area
100u" tin over 50u" nickel on solder area
BOARDLOCK: Brass, Tin Plated.
SCREWLOCK: Copper Alloy, Nickel Plated.
ELECTRICAL: Voltage Rating 250 V
Current Rating 3 AMP
Withstanding Voltage >1000 V RMS
Insulation Resistance >1000 M Ohms
Contact Resistance 20 mOhms max.
MARKING: Amphenol...(Series No.)
Commercial Reference
Manufacturing Date

PRODUCT CODE

L 77 HD X H XX S OL2 RM8

L: RoHS Compliant

77: tinned shell for receptable

HD : High density

Shell Size:
E, A, B, C, D

Mounting type:
H = rear insert 4-40

RM8 = retention clip + front screwlock

Termination
Straight for PCB

Contact type:
S = Socket

Configuration:
HD : 15,26,44,62,78

UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE
TOLERANCES		DRAWN	FILED	12/08/15
U.S.	METRIC			
X. +/-	0.38			
.X +/-	0.25			
.XX +/-	0.13			
FRACTIONS +/-	5°			
ANGLES +/-				
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :		
REMOVE SHARP EDGES		ANGLE OF PROJECTION		
DIMENSIONS				
U.S.	INCHES			
METRIC	MM			

Amphenol

TITLE
D-SUB connector, HD Series

SIZE	DRAWING NO.	REV.
A4	L77HDXHXXSOL2RM8	6
SCALE	SHEET 1 OF 1	
NONE		