



ISO9001-2015
Certificate No.672Q22020207194

No.T52210311961TC Date;OCT 12,2022 No.T52310270397TC Date:apr 15.2023

承認書

SPECIFICATION FOR APPROVAL

客户名稱
CUSTOMER

品名規格
DESCRIPTION RH3.5x9x0.8x2

客户料號
CUS. P/N

提出日期
DATE 2025.05.12

出 圖 RDAWING		
發 行 MADE	復 核 CHECKED	確 認 APPROVED
李光赫	方煜镗	梁琼
销售部：张 丽		

承 認 CUSTOMER APPROVE




深圳市航宇磁电有限公司

SPECIFICATION 產品規格書		DRAWING NO.: CK-RH3.5-9-0.8	
CUSTOMER			
CUSTOMER TYPE			
ITEM		RH3. 5×9×0. 8×2	
MATERIAL		CKA	
CUSTOMER P/N			
SCALE:	UNIT:	METHOD:	DATE:
NONE	mm	第三角法	2025.5.12
DRAWN/DATE	CHECK/DATE	APPROVED/DATE	ISSUE NO
梁琮	方煜鎰	李光赫	

1. DIMENSIONS:

ψA	ψB	C	D
3.50±0.15	9.00±0.30	28.00±0.30	5.0±1.0



深圳市航宇磁电有限公司

2. ELECTRONIC CHARACTERISTICS:

ITEM.	IMPEDANCE(Ω)
	100MHz
SPEC.	170 Ω MIN

3.NOTES:

(1) WIRE & WINDING: ψ CP0.6

(2) TEST FREQUENCY: 100MHZ.

(3) TEST METER: HP-4191A RF.

TEST DATA

ITEM.	ψA	ψB	C	D		
SPEC.	3.50 ± 0.15	9.00 ± 0.30	28.00 ± 0.30	5.0 ± 1.0		
01.	3.63	9.01	28.1	4.6		
02.	3.58	9.08	28.2	4.6		
03.	3.54	9.05	28.1	4.6		
04.	3.70	9.10	28.2	4.7		
05.	3.68	9.08	28.2	4.7		
06.	3.75	8.96	28.1	4.8		
07.	3.70	8.95	28.1	4.5		
08.	3.73	8.93	28.2	4.4		
09.	3.57	9.10	28.2	4.6		
10.	3.66	9.17	28.2	4.7		
ITEM.	IMPEDANC E(Ω)					
	100MHz					
SPEC.	170 Ω MIN					
1	198.86					
2	195.33					
3	202.88					
4	212.45					
5	210.23					
6	216.83					
7	205.65					
8	198.75					
9	206.36					
10	208.45					