









Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1



—NOTES—

1.Electrical:

Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.

2.Mechanical:

MATE AND UNMATE FORCE:
MATE FORCE:3.5kg MAX
UNMATE FORCE:0.05kg MIN
Durability:1500cycles MIN.

3.Environment:

Operating Temperature:−25°to+85°.


4.FINISH:

TERMINAL: C5191 GOLD Plated Over NICKEL
Contact area,
Plated ALL Over NICKEL.


Shell: SUS201 WITH NICKEL&GOLD Plated.

5.COLOR:

HOUSING:LCP,BLACK.




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05


TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X ± 0.30	X. $\pm 2^\circ$	PART NO. TF-021B-P8	TITLE: 2.65H TF 短体无侦测PIN		
.XX ± 0.20					
.XXX ± 0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

User Direction of Unreeling






- NOTES
- 1. NUMBER OF CONNECTORS:SEE TABLE 2
 - 2. LEAD TAPE LENGTH



COVER TAPE PEELING ANGLE:165°~180°
PEELING FORCE:20~130g
CARRIER TAPE

3.QUANTITY: 10REEL/CARTON



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
.X±0.30	X.*±2°	PART NO.		TITLE:		
.XX±0.20		TF-021B-P8		2.65H TF短体无检测PIN		
.XXX±0.10		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	2/2