



Silicon Planar Zener Diodes

FEATURES


- Total power dissipation: Max. 500mW.
- Wide zener reverse voltage range 2.4V to 51V.
- Small plastic package suitable for surface mounted design.
- Tolerance approximately $\pm 5\%$

MECHANICAL DATA

- Case: SOD-123W
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 16mg/0.00056oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Absolute Maximum Ratings And Characteristics ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Power Dissipation	P_{tot}	500	mW
Forward Voltage at $I_F = 10\text{ mA}$	V_F	0.9	V
Typical thermal resistance junction to ambient ⁽¹⁾	$R_{\theta JA}$	340	$^\circ\text{C/W}$
Operating and Storage Temperature Range	T_j, T_{stg}	-55 ~ +150	$^\circ\text{C}$

(1) Thermal resistance from junction to ambient at P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper areas pads.

Fig.1 Maximum Continuous Power Derating





Fig.2 Typical Transient Thermal Impedance



Characteristics at Ta = 25°C

Type	Marking	Zener Voltage Range ⁽¹⁾			I _{ZT}	Dynamic Impedance	Reverse Current	
		V _{ZT} (at I _{ZT})				Z _{ZT} (at I _{ZT})	I _R	at V _R
		Min (V)	Nom (V)	Max (V)	(mA)	Max (Ω)	Max (μA)	(V)
BZT52C2V4-VL	WX	2.28	2.4	2.56	5	100	120	1
BZT52C2V7-VL	W1	2.5	2.7	2.9	5	110	120	1
BZT52C3V0-VL	W2	2.8	3.0	3.2	5	120	50	1
BZT52C3V3-VL	W3	3.1	3.3	3.5	5	130	20	1
BZT52C3V6-VL	W4	3.4	3.6	3.8	5	130	10	1
BZT52C3V9-VL	W5	3.7	3.9	4.1	5	130	5	1
BZT52C4V3-VL	W6	4	4.3	4.6	5	130	5	1
BZT52C4V7-VL	W7	4.4	4.7	5	5	130	2	1
BZT52C5V1-VL	W8	4.8	5.1	5.4	5	130	2	1.5
BZT52C5V6-VL	W9	5.2	5.6	6	5	80	1	2.5
BZT52C6V2-VL	WA	5.8	6.2	6.6	5	50	1	3
BZT52C6V8-VL	WB	6.4	6.8	7.2	5	30	0.5	3.5
BZT52C7V5-VL	WC	7	7.5	7.9	5	30	0.5	4
BZT52C8V2-VL	WD	7.7	8.2	8.7	5	30	0.5	5
BZT52C9V1-VL	WE	8.5	9.1	9.6	5	30	0.5	6
BZT52C10-VL	WF	9.4	10	10.6	5	30	0.1	7
BZT52C11-VL	WG	10.4	11	11.6	5	30	0.1	8
BZT52C12-VL	WH	11.4	12	12.7	5	35	0.1	9
BZT52C13-VL	WI	12.4	13	14.1	5	35	0.1	10
BZT52C15-VL	WJ	13.8	15	15.6	5	40	0.1	11
BZT52C16-VL	WK	15.3	16	17.1	5	40	0.1	12
BZT52C18-VL	WL	16.8	18	19.1	5	45	0.1	13
BZT52C20-VL	WM	18.8	20	21.2	5	50	0.1	15
BZT52C22-VL	WN	20.8	22	23.3	5	55	0.1	17
BZT52C24-VL	WO	22.8	24	25.6	5	60	0.1	19
BZT52C27-VL	WP	25.1	27	28.9	5	70	0.1	21
BZT52C30-VL	WQ	28	30	32	5	80	0.1	23
BZT52C33-VL	WR	31	33	35	5	80	0.1	25
BZT52C36-VL	WS	34	36	38	5	90	0.1	27
BZT52C39-VL	WT	37	39	41	2.5	100	2	30
BZT52C43-VL	WU	40	43	46	2.5	130	2	33
BZT52C47-VL	WV	44	47	50	2.5	150	2	36
BZT52C51-VL	WW	48	51	54	2.5	180	1	39


(1) V_{ZT} is tested with pulses (20 ms)



PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-123W



SOD-123W mechanical data

UNIT		A	C	D	E	E ₁	L ₁	b	A ₁	∠
mm	max	1.3	0.22	1.8	2.8	3.9	0.45	0.7	0.2	9°
	min	0.9	0.09	1.5	2.5	3.6	0.25	0.5	—	
mil	max	51	8.7	71	110	154	18	28	8	
	min	35	3.5	59	98	142	10	20	—	

The recommended mounting pad size

