




F

E

D

C

B

A

F

E

D

C

B

A

电机参数表Motor Parameter Table			
1	额定电压Nominal Voltage	48	VDC
2	额定转矩Nominal Torque	177	mNm
3	额定转速Nominal Speed	6996	rpm
4	额定电流Nominal Current	3.2	A
5	空载转速No-load Speed	7891	rpm
6	空载电流No-load Current	0.11	A

编码器参数表Encoder Parameter Table			
1	编码器类型Encoder Type	增量差分 Incremental (Differential Output)	
2	供电电压Power Supply Voltage	5	V
3	分辨率Encoder Resolution	500线 (500)	

LEC-接线定义									
电机焊接定义					编码器焊接定义				
红		黑			红	黑	黄	灰	绿
Red		Black			Red	Black	Yellow	Grey	Green
电源正		电源负			5V	GND	A+	A-	B+
Power Positive		Power Negative					B-	Z+	Z-

制图	版次	比例	型号规格 (Model/Specification)	
Drawn	Revision	Scale		
审核	投影		HM-DCX-D35mm	
Reviewed	General tolerance		品名 (Product Name)	
批准	X.	长度	石墨电刷电机	
Approved		±0.2	(Graphite brush motor)	
		*为重点尺寸		
		* Critical dimension		
		单位Unit	成都恒利泰科技有限公司	
		mm	Chengdu HenryTech Technology co., Ltd	