

Surface Mounted Schottky Barrier Rectifiers

Reverse Voltage - 40V ~ 100V


Forward Current - 20 A

FEATURES

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ For surface mounted applications
- ◆ Built-in strain relief, ideal for automated placement
- ◆ Low forward voltage drop
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed
250°C/10 seconds at terminals

MECHANICAL DATA

- ◆ Case: Molded plastic body
- ◆ Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- ◆ Polarity: Polarity symbol marking on body
- ◆ Mounting Position: Any
- ◆ Weight: 0.003 ounce, 0.092 grams



Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	20L40SP	20L45SP	20L50SP	20L60SP	20L80SP	20L100SP	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	40	45	50	60	80	100	V
Maximum RMS voltage	V _{RMS}	28	31.5	35	42	56	70	V
Maximum DC blocking voltage	V _{DC}	40	45	50	60	80	100	V
Maximum average forward rectified current at T _L =100℃	I _(AV)	20.0						A
Peak forward surge current,8.3ms single half sine-wave superimposed on rated load	I _{FSM}	300.0						A
Maximum instantaneous forward voltage at2.0A at20.0A	V _F	0.35 0.48			0.40 0.55	0.45 0.70		V
Maximum DCreverse current T _A =25℃ at rated DC blocking voltage T _A =125℃	I _R	0.5 50				0.2 20		mA
Typical thermal resistance	R _{qJA}	60.0						℃/W
Operating junction temperature range	T _J	-55 to +150						℃
Storage temperature range	T _{STG}	-55 to +150						℃

Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS



Marking Diagram



Ordering information


Package	Packing Description	Packing Quantity
TO-277	Tape/Reel, 13"reel	5000PCS/Reel 50000PCS/Carton

Package Dimensions

TO-277

Dim.	Millimeter(mm)		mil	
	Min.	Max.	Min.	Max.
A	1.1	1.2	43	47
A2	0.3	0.4	12	16
b1	0.8	1	32	39
b2	1.7	1.9	67	75
D	3.9	4.1	154	162
D1	3.054		120	
E	6.4	6.6	252	260
e	1.84		73	
E1	5.3	5.5	209	217
E2	3.549		140	
L	0.8	1	32	39
L1	0.5	0.7	20	28
W	1.1	1.4	43	55

The recommended mounting pad size



Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.