











3D View



PIN DEFINE TABLE

PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	—	B2	—
A10	—	B3	—
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D—	B6	D+
A6	D+	B7	D—
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	—	B10	—
A2	—	B11	—
A1	GND	B12	GND

SPECIFICATION:

- MATERIAL & FINISH:SEE THE LIST;
- PLATING SPECIFICATION:
 - CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Au PLATED ON THE SOLDER AREA.
 - SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE:CLEAR ONLY
- MECHANICAL:
 - MATING FORCE:0.5~2.0kgf;
 - UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
 - DURABILITY:10000 CYCLES;
- ELECTRICAL:
 - CURRENT RATING:5A Max;
 - VOLTAGE RATING:20V Max;
 - DIELECTRIC WITHSTANDING VOLTAGE:100VAc;
 - CONTACT RESISTANCE:40mΩ Ohms Max.;
 - INSULATION RESISTANCE:100M Ohms Min.;
- ENVIRONMENTAL:
 - OPERATING TEMPERATURE:−40°C~+85°C;
 - WETTING TEMPERATURE:265±5°C,5±0.5s
 - Salt Spray Test:48H Min

P/N	DIM.H	DIM.A	Remark
TYPE-C-630-LDRH100-B	10.0	4.50	LCP BLACK
TYPE-C-630-LDRH100-O	10.0	4.50	PA10T ORANGE
TYPE-C-630-LDRH105-B	10.5	5.00	LCP BLACK

NO.	PART NAME	Q'TY	MATERIAL	FINISH
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	14	Copper Alloy,T=0.15mm	Au/Sn/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:TYPE-C 16P直立式 DIP型
插座 H10.0&10.5mm

DECIMALS:

ANGLES:

X.:±0.50

X':±5°

X.X:±0.35

X.X':±3°

X.XX:±0.25

X.XX':±2.5°

PAR

TYPE-C-630-LDRHXXX-X

DWN

Lucas

CHKD

Ethan

APVD

Jacob




SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F2

REV:A



说明:

1. 每卷前后各空10PCS,尾部用美纹胶纸封住;
2. 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
3. 每10卷盘一叠共3000Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高),不可重压;
6. 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a. 产品不可跑下带凹槽;
b. 产品不可有摔伤,变形;
c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		2500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.35

X.XX:±0.25

ANGLES:

X':±5°

X.X':±3°

X.XX':±2.5°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdTITLE:TYPE-C 16P直立式DIP型
插座 H10.0&10.5mm—包装图

PAR TYPE-C-630-LDRHXXX-X

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:2F2

REV:A