

Features

- Low operating voltage: 10V
- Ultra low capacitance: 0.25pF(Typ)
- Ultra low leakage: nA level
- Low clamping voltage
- -IEC 61000-4-2 (ESD) immunity test
 - Air discharge: $\pm 30\text{kV}$
 - Contact discharge: $\pm 30\text{kV}$
- -IEC61000-4-4 (EFT) 40A (5/50ns)
- -IEC61000-4-5 (Lightning) 6 A (8/20 μs)
- 2-pin leadless package
- These are Pb-Free Devices
- Response Time is Typically < 1 ns


Mechanical Characteristics

- Package: DFN0603-2(0201)
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound
- Terminal Connections: See Diagram Below
- -IEC 61000-4-2 (ESD) immunity test

Applications

- RF antenna
- USB 3.2 Gen 1 and Gen 2
- Ethernet 1000 BASE-T
- Ethernet 10G BASE-T
- Display port

Dimensions and Pin Configuration



Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	P _{pk}	100	W
Peak Pulse Current (8/20μs)	I _{pp}	6	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±30 ±30	KV
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V _{RWM}	--	--	10	V	
Breakdown Voltage	V _{BR}	12.5			V	I _T = 1mA
Reverse Leakage Current	I _R	--	--	200	nA	V _{RWM} = 10V
Clamping Voltage	V _C	--	12	15	V	I _{pp} = 1A (8x 20us pulse)
Clamping Voltage	V _C	--	16	20	V	I _{pp} = 5.5A (8x 20us pulse)
Junction Capacitance	C _J	--	0.25	0.4	pF	V _R = 0V, f = 1MHz

Electrical Characteristics

Symbol	Parameter
V _{BR}	Reverse Breakdown Voltage
I _{BR}	Reverse Breakdown Current
V _{RWM}	Reverse Stand-off Voltage
I _R	Reverse Leakage Current
V _H	Holding Voltage
I _H	Holding Current
V _T	Trigger Voltage
I _T	Trigger Current
I _{PP}	Peak Pulse Current
V _{CL}	Clamping Voltage



Characteristic Curves

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve




Package Outline & Dimensions

DFN0603-2 (0201)



SYM	DIMENSIONS		
	MILLIMETERS		
	MIN	NOM	MAX
A	0.230	0.300	0.330
A1	0.000	0.020	0.050
b	0.215	0.245	0.275
c	0.120	0.150	0.180
D	0.550	0.600	0.650
e	0.355 BSC		
E	0.250	0.300	0.350
L	0.160	0.190	0.220
h	0.079 BSC		

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.30	0.012
Y1	0.25	0.010
Y2	0.15	0.006
Y3	0.40	0.016
Z	0.65	0.026